

# FMW22S010-3 DATA SHEET

# WR-22 Waveguide Section 3 Inch Straight Length with UG-383/U Round Cover Flange from 33 GHz to 50 GHz

Fairview Microwave's FMW22S010-3 is a 3 inch WR-22 straight waveguide section that operates from 33 GHz to 50 GHz. This straight waveguide section offers a typical 0.25 dB insertion loss and a maximum 1.06 VSWR. The input of this straight waveguide section has a UG-383/U Round Cover flange. FMW22S010-3 is part of over 40,000 RF, microwave and millimeter wave components. Our WR-22 straight waveguide section will ship worldwide the same day it is purchased along with our other RF components.

## **Electrical Specifications\***

Description	Min	Тур	Max	Units
Frequency Range	33		50	GHz
VSWR			1.1:1	
Insertion Loss		0.25		dB

<sup>\*</sup> Values at 25°C, sea level

### **Mechanical Specifications**

Waveguide Size WR-22

Section Length 3 in [76.2 mm]

Flange 1

Flange Type Round Cover
Flange Designation UG-383/U
Material Brass Copper

Plating Gold

Waveguide

Interface WR-22

Material Brass Copper

Plating Gold

Flange 2

Flange Type Round Cover
Flange Designation UG-383/U
Material Brass Copper
Plating Gold

**Compliance Certifications** (see product page for current document)

#### **Plotted and Other Data**

Notes:

Values at 25 °C, sea level



#### Features:

- 3" Length
- WR-22 Waveguide
- 33 GHz to 50 GHz Frequency Range
- UG-383/U Round Cover Flange
- Comprehensive waveguide offering also includes E-Bends, H-Bends, Waveguide to Coax Adapters, Filters, Terminations, and more.

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com

Copyright © 2019





WR-22 Waveguide Section 3 Inch Straight Length with UG-383/U Round Cover Flange from 33 GHz to 50 GHz from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: WR-22 Waveguide Section 3 Inch Straight Length with UG-383/U Round Cover Flange from 33 GHz to 50 GHz FMW22S010-3

URL: https://www.fairviewmicrowave.com/wr-22-waveguide-section-straight-ug383-round-fmw22s010-3-p.aspx





301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2019









\*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

Fairview Microwave	NOTES:  1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  3. DIMENSIONS ARE IN INCHES [mm].								
■ an INFINIT® brand  TITLE  WR-22 Waveguide Section 3 Inch Straight Length with	DWG NO FMW22S010-3				CAGE CODE 3FKR5				
UG-383/U Round Cover Flange from 33 GHz to 50 GHz	CAD FILE	07/03/19	SHEET	1 OF 1	SCAL	E N/A	SIZE A	7361	