

# FMW28AT001-30 DATA SHEET

# WR-28 Waveguide Continuously Variable Attenuator with Dial 0 to 30 dB Operating from 26.5 GHz to 40 GHz, UG-599/U Square Cover Flange

Fairview Microwave's Continuously Variable Waveguide Attenuators are offered for the frequency range of 18 to 110 GHz in different waveguide bands. The attenuation value of the Continuously Variable attenuators are from 0 to 30 dB with full waveguide operational bandwidth. The Continuously Variable attenuators are equipped with a micrometer, which enables rapid re-setting. With calibrated charts, attenuators can be used as direct reading attenuator for bench top test set use. The level setting attenuators are typically used in the test setups and prototype assemblies where certain attenuation is required.

# **Electrical Specifications\***

Description	Min	Тур	Max	Units
Frequency Range	26.5		40	GHz
Typical Attenuation Value	0		30	dB
Insertion Loss		0.3		dB
Input Power (CW)			5	Watts
VSWR		1.15:1		

Values at 25°C, sea level

# **Mechanical Specifications**

## Flange 1

Interface UG-599/U Material Brass Plating Gold

### Waveguide

Interface WR-28
Material Copper
Plating Gold

#### Flange 2

Interface UG-599/U Material Brass Plating Gold

#### Size

 Length
 2.75 in [69.85 mm]

 Width
 1.375 in [34.93 mm]

 Height
 2.572 in [65.33 mm]

 Weight
 0.22 lbs [99.79 g]

**Compliance Certifications** (see product page for current document)

## **Plotted and Other Data**

Notes:

• Values at 25 °C, sea level



#### Features:

- 30 dB Attenuation Level
- Rotary Dial for Continuous Adjustments
- Frequency Range: 26.5 GHz to 40 GHz
- Typical VSWR 1.15:1
- Max Power Rating: 5 Watts (CW)

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com






WR-28 Waveguide Continuously Variable Attenuator with Dial 0 to 30 dB Operating from 26.5 GHz to 40 GHz, UG-599/U Square Cover Flange from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF ondemand.

For additional information on this product, please click the following link: WR-28 Waveguide Continuously Variable Attenuator with Dial 0 to 30 dB Operating from 26.5 GHz to 40 GHz, UG-599/U Square Cover Flange FMW28AT001-30

URL: https://www.fairviewmicrowave.com/wr-28-waveguide-continuously-variable-attenuator-30-db-ug599-square-fm-w28at001-30-p.aspx



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689



# FMW28AT001-30 DATA SHEET

