

FMW28S010-3 **DATA SHEET**

WR-28 Waveguide Section 3 Inch Straight Length with UG-599/U Square Cover Flange from 26.5 GHz to 40 GHz

Fairview Microwave's FMW28S010-3 is a 3 inch WR-28 straight waveguide section that operates from 26.5 GHz to 40 GHz. This straight waveguide section offers a typical 0.20 dB insertion loss and a maximum 1.06 VSWR. The input of this straight waveguide section has a UG-599/U Square Cover flange. FMW28S010-3 is part of over 40,000 RF, microwave and millimeter wave components. Our WR-28 straight waveguide sefction will ship worldwide the same day it is purchased along with our other RF components.



Description	Min	Тур	Max	Units
Frequency Range	26.5		40	GHz
VSWR			1.06:1	
Insertion Loss		0.2		dB

^{*} Values at 25°C, sea level

Mechanical Specifications

Waveguide Size WR-28

Section Length 3 in [76.2 mm]

Flange 1

Flange Type Square Cover Flange Designation UG-599/U Material **Brass Copper**

Plating Gold

Waveguide

Interface WR-28 Material **Brass Copper**

Plating Gold

Flange 2

Flange Type Square Cover Flange Designation UG-599/U Material **Brass Copper Plating** Gold

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Values at 25 °C, sea level



Features:

- 3" Length
- WR-28 Waveguide
- 26.5 GHz to 40 GHz Frequency Range
- UG-599/U Square Cover Flange
- Comprenhensive waveguide offering also includes E-Bends, H-Bends, Waveguide to Coax Adapters, Filters, terminations, and more.

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com





WR-28 Waveguide Section 3 Inch Straight Length with UG-599/U Square Cover Flange from 26.5 GHz to 40 GHz from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: WR-28 Waveguide Section 3 Inch Straight Length with UG-599/U Square Cover Flange from 26.5 GHz to 40 GHz FMW28S010-3


The information contained in this document is accurate to the best of our knowledge and representative of the part

URL: https://www.fairviewmicrowave.com/wr-28-waveguide-section-straight-ug599-square-fmw28s010-3-p.aspx

described	herein. It may be necessa	ry to make r	modifications to the par	t and/or t	the documentation of the par	t, in order
to implen	nent improvements. Fairvie	w Microwave	reserves the right to m	ake such	changes as required. Unless	otherwise
stated, al	I specifications are nominal	. Fairview M	licrowave does not mal	ce any rep	presentation or warranty reg	arding the
				airview M	icrowave does not assume a	ny liability
arising ou	it of the use of any part or o	locumentatio	n.			







WR-28 Waveguide Section 3 Inch Straight Length with UG-599/U Square Cover Flange from 26.5 GHz to 40

■■■ Fairview Microwave

an INFINIT© brand

TITLE

GHz

CAD FILE 07/05/19

DWG NO

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.

2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.

3. DIMENSIONS ARE IN INCHES [mm].

1 OF 1

FMW28S010-3

SHEET

CAGE CODE

SIZE A

SCALE N/A

3FKR5

7361