

FMW8TW0000 DATA SHEET

WR-8 45 Degree Waveguide Right-hand Twist Using a UG-387/U-Mod Flange and a 90 GHz to 140 GHz Frequency Range

Fairview's Microwave FMW8TW0000 is a 45 degree, Right Hand, WR-8 waveguide twist that operates from 90 GHz to 140 GHz. This waveguide twist offers a typical 0.3 dB insertion loss and a typical 1.15 VSWR. The input of this waveguide twist has a UG-387/U-M Flange. FMW8TW0000 is part of over 40,000 RF, microwave and millimeter wave components. Our WR-8 waveguide twist will ship worldwide the same day it is purchased along with our other RF components.

Electrical Specifications

| Description | Min | Тур | Max | Units |
|-----------------|-----|--------|-----|-------|
| Frequency Range | 90 | | 140 | GHz |
| VSWR | | 1.15:1 | | |
| Insertion Loss | | 0.3 | | dB |
| | | | | |

Electrical Specification Notes:

VSWR measurement is the representation of the load used for testing

| Mechanical Specificati Waveguide Size Section Length | ons | WR-8 1.25 in [31.7! | 5 mm] |
|---|---------------------|------------------------|---------------------|
| Description | Flange 1 | Waveguide | Flange 2 |
| Interface | JG-387/U-Mod | WR-8 | UG-387/U-Mod |
| Material Oxyge | en Free Hard Copper | Oxygen Free Hard | d CopperOxygen Free |
| Hard Copper | | | |
| Plating | Gold | Gold | Gold |
| Color | Gold | Gold | Gold |

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

• Notes, Plotted Data



Features:

- WR-8 Waveguide
- 90 to 140 GHz Frequency Range
- UG-387/U-Mod Flange
- 45° Right Hand (Clockwise) Twist
- 1.15:1 Typical VSWR

Applications:

- Instrumentation
- Precision measurements
- Prototyping and characterization

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com





WR-8 45 Degree Waveguide Right-hand Twist Using a UG-387/U-Mod Flange and a 90 GHz to 140 GHz Frequency Range from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: WR-8 45 Degree Waveguide Right-hand Twist Using a UG-387/U-Mod Flange and a 90 GHz to 140 GHz Frequency Range FMW8TW0000

URL: https://www.fairviewmicrowave.com/wr-8-45-waveguide-twist-ug387mod-90-140-ghz-fmw8tw0000-p.aspx









| Fairview Microwave | NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm]. | | | | | | |
|---|---|--------------|-------|-----------------|--------|------|--|
| WR-8 45 Degree Waveguide Right-hand Twist Using a UG-387/U-Mod Flange and a 90 GHz to 140 GHz Frequency Range | DWG NO FMW8TW0000 | | | CAGE CODE 3FKR5 | | | |
| | CAD FILE 08/05/19 | SHEET 1 OF 1 | SCALI | E N/A | SIZE A | 7361 | |