

FMWCA1026 DATA SHEET

WR-42 to SMA Female Waveguide to Coax Adapter UG-597/U Square Cover with 18 GHz to 26.5 GHz K Band in Aluminum, Paint

The FMWCA1026 is a waveguide to coaxial adapter operating in the K Band with a 18 to 26.5 GHz frequency range. This adapter offers a WR-42 waveguide interface size using a standard UG-597/U Square Cover Flange. The FMWCA1026 is constructed of Aluminum Alloy and painted to ensure durability. The coaxial connector offered by this adapter uses a SMA Female Connector.

Configuration

Waveguide Size WR-42

Flange UG-597/U Square Cover

RF Connector
Impedance
Body Geometry

SMA Female
50 Ohms
Right Angle

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	18		26.5	GHz
VSWR		1.03:1		
			<u> </u>	

Mechanical Specifications

RF Connector

Connector Type SMA Female

Waveguide Interface

Waveguide Type WR-42

Flange Type Square Cover
Flange Designation UG-597/U
Body Material and Plating Aluminum, Paint

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Values at +25 °C, sea level unless stated otherwise



Features:

- K Band
- 18 to 26.5 GHz
 Frequency Range
- WR-42 Waveguide Interface
- UG-597/U Square Cover Flange
- SMA Female RF Interface
- · Right Angle

Applications:

- Test Benches
- Radar
- Satellite
- · Microwave Radio Systems
- Military and Space
- Communication Systems

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com



Typical Performance Data



WR-42 to SMA Female Waveguide to Coax Adapter UG-597/U Square Cover with 18 GHz to 26.5 GHz K Band in Aluminum, Paint from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: WR-42 to SMA Female Waveguide to Coax Adapter UG-597/U Square Cover with 18 GHz to 26.5 GHz K Band in Aluminum, Paint FMWCA1026

URL: https://www.fairviewmicrowave.com/wr42-sma-female-waveguide-coax-adapter-ug597-square-fmwca1026-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.







STANDARD TOLERANCES

.X ±0.2 .XX ±0.01 .XXX ±0.005

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

