

4 Way Power Divider SMA Connectors From 2 GHz to 18 GHz Rated at 30 Watts

Fairview Microwave carries a wide selection of power dividers to fit your needs. These components are essential in many systems, allowing the combination of multiple signals or splitting of a single signal into multiple signals with equal magnitude and phase. Fairview Microwave's resistive and reactive power dividers come with excellent performance featuring minimal loss, high isolation and low VSWR. They are available in both narrow and broad bandwidths with a variety of connector types.

The MP0218-4 is a 4 way reactive power divider that operates from 2 to 18 GHz and can handle up to 30 Watts (CW). This SMA power divider offers 16 dB min isolation and 1.65:1 max VSWR. The package interface uses SMA inputs on all of the ports.

Electrical Specifications

Design: Reactive
 Number of Output Ports: 4

Description	Min	Typ	Max	Units
Frequency Range	2		18	GHz
Impedance		50		Ohms
Input VSWR			1.65:1	
Output VSWR			1.65:1	
Insertion Loss			8.2	dB
Isolation	16			dB
Amplitude Balance			±0.6	dB
Phase Balance			±10	Degrees
Input Power (CW)			30	Watts

Electrical Specification Notes:
 Values at +25°C, sea level.
 Insertion loss includes 6dB theoretical loss.

Mechanical Specifications

Size
 Length: 2.72 in [69.09 mm]
 Width: 2.36 in [59.94 mm]
 Height: 0.39 in [9.91 mm]
 Weight: 0.239 lbs [108.41 g]

Configuration
 Input Connector: SMA Female
 Output Connectors: SMA Female

Environmental Specifications

Temperature
 Operating Range: -55 to +125 deg C
 Storage Range: -55 to +100 deg C



Features:

- 4-Way Power Divider
- Reactive Design
- 2 GHz to 18 GHz Frequency Range
- Max Power 30W (CW)
- Isolation > 16 dB

Applications:

- Test and Measurement
- Military Communications
- Commercial Communications
- Wireless Communications
- SATCOM


Fairview Microwave
 1130 Junction Dr. #100
 Allen, TX 75013
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Typical Performance Data




4 Way Power Divider SMA Connectors From 2 GHz to 18 GHz Rated at 30 Watts from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [4 Way Power Divider SMA Connectors From 2 GHz to 18 GHz Rated at 30 Watts MP0218-4](#)

URL: <https://www.fairviewmicrowave.com/4-way-power-divider-sma-18-ghz-30-watts-mp0218-4-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].		
TITLE 4 Way Power Divider SMA Connectors From 2 GHz to 18 GHz Rated at 30 Watts		DWG NO MP0218-4		CAGE CODE 3FKR5
		CAD FILE 011415	SHEET	SCALE N/A SIZE A 5568