

**N Female Open Circuit Connector Cap With 2.75 Inch Chain**

RF connector dust cap SC2019C from Fairview Microwave is constructed with an N connection and has a female gender. This N female dust cap is designed as non-shorting and the body is nickel plated to ensure its durability. The non-shorting N connector cap from Fairview Microwave is designed with a 2.75 inch chain and is in-stock for same day shipment.

RF dust caps are essential for precision connectors to protect them from dust, corrosion and other potential damage especially when using on test and measurement equipment. Some RF connector cap models are designed with a chain to prevent loss or misplacement. Internal shorting connector cap models are available and help to protect equipment from a spike in current commonly caused by ESD (Electro Static Discharge).

**Mechanical Specifications**

**Configuration**

Connector N Female Non-shorting  
 Chain Option 2.75 in Chain

Description	Material	Plating
Body	Brass	Nickel 100µ" min.
Chain	Brass	Nickel
Rivet	Brass	Nickel

**Size**

Length 0.57 in [14.48 mm]  
 Width 0.71 in [18.03 mm]  
 Weight 0.038 lbs [17.24 g]

**Environmental Specifications**

**Temperature**

Operating Range -65 to +165 deg C

**Compliance Certifications** (visit [www.FairviewMicrowave.com](http://www.FairviewMicrowave.com) for current document)

RoHS Compliant Yes  
 REACH Compliant 12/17/2015



**Features:**

- Protects against dust and contaminants
- Protects against physical damage
- Nickel Plated Body
- Chain Included

**Applications:**

- General Purpose Laboratory Use
- Test and Measurement

Fairview Microwave  
 1130 Junction Dr. #100  
 Allen, TX 75013  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

**Plotted and Other Data**


Notes:

N Female Open Circuit Connector Cap With 2.75 Inch Chain from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [N Female Open Circuit Connector Cap With 2.75 Inch Chain SC2019C](#)

URL: <https://www.fairviewmicrowave.com/n-female-open-circuit-connector-cap-2-inch-chain-sc2019c-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



**STANDARD TOLERANCES**

.X	±0.2
.XX	±0.1
.XXX	±0.05

\*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

<b>FAIRVIEW MICROWAVE INC.</b> ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE N Female Open Circuit Connector Cap With 2.75 Inch Chain		DWG NO SC2019C		CAGE CODE 3FKR5	
CAD FILE	060816	SHEET	SCALE	N/A	SIZE A 3045