

2 Way Power Divider SMA Connectors From 800 MHz to 2.4 GHz Rated at 20 Watts

Fairview Microwave carries a wide selection of power dividers to fit your needs. These components are essential in many systems, allowing the combination of multiple signals or splitting of a single signal into multiple signals with equal magnitude and phase. Fairview Microwave's resistive and reactive power dividers come with excellent performance featuring minimal loss, high isolation and low VSWR. They are available in both narrow and broad bandwidths with a variety of connector types.

The MP8305-2 is a 2 way reactive power divider that operates from 800 MHz to 2.4 GHz and can handle up to 20 Watts (CW). This SMA power divider offers 20 dB min isolation and 1.3:1 max VSWR. The package interface uses SMA inputs on all of the ports.

Electrical Specifications

Design Reactive Number of Output Ports 2 Description Min Max Units Тур Frequency Range 0.8 2.4 GHz Impedance 50 Ohms Input VSWR 1.3:1 Output VSWR 1.2:1 Insertion Loss 3.4 dB Isolation 20 dB Amplitude Balance ±0.2 dB Phase Balance ±2 Degrees Input Power (CW) 20 Watts

Electrical Specification Notes: Values at +25°C, sea level. Insertion loss includes 3dB theoretical loss.

Mechanical Specifications

Size	
Length	1.38 in [35.05 mm]
Width	1.1 in [27.94 mm]
Height	0.39 in [9.91 mm]
Weight	0.053 lbs [24.04 g]
Configuration	
Input Connector	SMA Female

Input Connector Output Connectors

Environmental Specifications

Temperature Operating Range



Features:

- 2-Way Power Divider
- Reactive Design
- 800 MHz to 2.4 GHz Frequency Range
- Max Power 20W (CW)
- Isolation > 20 dB

Applications:

- Test and Measurement
- Military Communications
- Commercial Communications
- Wireless Communications
- SATCOM

-55 to 125 dea C

SMA Female

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com

MP8305-2 DATA SHEET





Compliance Certifications (see product page for current document)

Plotted and Other Data


Notes:

2 Way Power Divider SMA Connectors From 800 MHz to 2.4 GHz Rated at 20 Watts from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 2 Way Power Divider SMA Connectors From 800 MHz to 2.4 GHz Rated at 20 Watts MP8305-2

URL: https://www.fairviewmicrowave.com/2-way-power-divider-sma-2.4-ghz-20-watts-mp8305-2-p.aspx


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

an INFINIT© brand





301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689