



SMP Female Connector Solder Attachment For RG405, RG405 Tinned, .086 SR Cable

SMP female connector with solder/solder attachment for RG405, RG405 Tinned and .086 SR, part number SC5152, from Fairview Microwave is in-stock and ships same day. This SMP female connector operates up to a maximum frequency of 18 GHz and offers good VSWR of 1.3:1. This blind mate connector is ideal for applications without direct visual or tactile access to the connection point, for example, when two circuit boards need to be mated.

Fairview's SMP female connector SC5152 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		18	GHz
VSWR			1.3:1	
Operating Voltage (AC)			335	Vrms

Mechanical Specifications

Size

 Length
 0.25 in [6.35 mm]

 Width/Dia.
 0.131 in [3.33 mm]

 Weight
 0.0155 lbs [7.03 q]

Material Specifications

Description	Material	Plating		
Contact	Beryllium Copper	Gold 30 µin minimum		
	PTFE	30 µm minim		
Outer Conductor	Beryllium Copper	Gold		
	. 2	3 µin minimum		

Environmental Specifications

Temperature

Operating Range -65 to +165 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:



Configuration:

- SMP Female Connector
- MIL-STD-348A
- 50 Ohms
- Straight Body Geometry
- RG405, RG405 Tinned, .086 SR Interface Type
- Solder/Solder Attachment

Features:

- Operating Frequency of 18 GHz Max.
- Good VSWR of 1.3:1
- · Blind Mate Connector
- Gold Plated Beryllium Copper Contact
- · 30 µin minimum contact plating

Applications:

- General Purpose Test
- Custom Cable Assemblies

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com






Assembly Instruction

SMP Female Connector Solder Attachment For RG405, RG405 Tinned, .086 SR Cable from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: SMP Female Connector Solder Attachment For RG405, RG405 Tinned, .086 SR Cable SC5152

URL: https://www.fairviewmicrowave.com/smp-female-standard-rg405-connector-sc5152-p.aspx









STANDARD TOLERANCES

.X ±0.2 .XX ±0.01 .XXX ±0.005

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

Fairview Microwave	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
SMP Female Connector Solder Attachment For RG405, RG405 Tinned, .086 SR Cable	DWG NO SC5125			CAGE CODE 3FKR5		
	CAD FILE 04/11/18	SHEET 1 OF 1	SCAL	E N/A	SIZE A	7361