

# BNC Male Connector Crimp/Solder Attachment For RG316, RG174, RG188, 0.100 inch, LMR-100, LMR-100A, LMR-100A-FR Cable

BNC male connector with crimp/solder attachment for RG316, RG174, RG188, 0.100 inch, LMR-100, LMR-100A and LMR-100A-FR, part number SC6031, from Fairview Microwave is in-stock and ships same day. This BNC male connector operates up to a maximum frequency of 3 GHz and offers excellent VSWR of 1.25:1.

Fairview's BNC male connector SC6031 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

### **Electrical Specifications**

Description	Min	Тур	Max	Units
Frequency Range	DC		3	GHz
VSWR			1.25:1	
Operating Voltage (AC)			335	Vrms

### **Mechanical Specifications**

Size	
Length Width/Dia.	0.846 in [21.49 mm] 0.571 in [14.50 mm]
Weight	0.027 lbs [12.25 g]

### **Material Specifications**

Description	Material	Plating	
Contact	Brass	Gold 50 µin minimum	
Insulation	PTFE		
Body	Brass	Nickel 100 µin minimum	
Coupling Nut	Brass	Nickel 100 µin minimum	

### **Environmental Specifications**

Temperature

Operating Range

-65 to +165 deg C

**Compliance Certifications** (see product page for current document)

## **Plotted and Other Data**

Notes:





## **Configuration:**

- BNC Male Connector
- MIL-STD-348A
- 50 Ohms
- Straight Body Geometry
- RG316, RG174, RG188, 0.100 inch, LMR-100, LMR-100A, LMR-100A-FR Interface Type
- Crimp/Solder Attachment

### **Features:**

- Operating Frequency of 3 GHz Max.
- Excellent VSWR of 1.25:1
- Gold Plated Brass Contact
- 50 µin minimum contact plating

## **Applications:**

- General Purpose Test
- Custom Cable Assemblies

REV 2.1 Page 1 of 3 Copyright © 2017

Tel: 1-800-715-4396 / (972) 649-6678

Fairview Microwave 1130 Junction Dr. #100

Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com

Allen, TX 75013






#### **Assembly Instruction**

BNC Male Connector Crimp/Solder Attachment For RG316, RG174, RG188, 0.100 inch, LMR-100, LMR-100A, LMR-100A-FR Cable from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: BNC Male Connector Crimp/Solder Attachment For RG316, RG174, RG188, 0.100 inch, LMR-100, LMR-100A, LMR-100A-FR Cable SC6031


URL: https://www.fairviewmicrowave.com/bnc-male-standard-rg316-rg174-connector-sc6031-p.aspx



1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689