

SD8267 DATA SHEET

50 ohm 2.92mm plug to 2.92mm jack DC Block inner, 10MHz to 40GHz VSWR1.3, rated 50 Volt in Stainless Steel

Fairview Microwave SD8267 is an inner DC block with 2.92mm connectors. It has a blocking capacitor on the inner conductor and operates from 10 MHz to 40 GHz. Our 2.92mm DC block offers good insertion loss of 1.3 dB and has a maximum operating voltage of 50 Vdc. DC blocks are commonly used to filter out unwanted DC signals, while allowing AC drive signals to pass through. They can help improve signal to noise ratio (SNR), eliminate ground loops, or provide isolation in your test setup. All of Fairview Microwave DC blocks are in stock and available to ship same-day.

Electrical Specifications

Description	Min	T	ур	Max	U	nits
Frequency Range	0.01			40		GHz
Impedance		5	0		С	hms
VSWR				1.3:1		
Insertion Loss				1.3		dB
Operating Voltage (DC)				50	\	olts/

Mechanical Specifications

Size	
Length	0.835 in [21.21 mm]
Width	0.315 in [8 mm]
Height	0.315 in [8 mm]
Weight	0.1 lbs [45.36 g]

Housing Material and Plating

Stainless Steel

Configuration

Package Type

Connectorized

Description	Connector 1	Connector 2
Туре	2.92mm Male	2.92mm Female
Inner Cond Material & Plati	ng Beryllium Copper, Gold	Beryllium Copper, Gold

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:



Features:

- Inner DC Blocks with Stainless
 Steel Body
- 2.92mm connectorized configuration
- Operates from 10 MHz to 40 GHz
- 50 Ohm Impedance

Applications:

- Test & Measurement
- Ground Loop Elimination
- Signal to Noise Ratio (SNR) Improvement

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com





50 ohm 2.92mm plug to 2.92mm jack DC Block inner, 10MHz to 40GHz VSWR1.3, rated 50 Volt in Stainless Steel from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

Click the following link to obtain additional part information: 50 ohm 2.92mm plug to 2.92mm jack DC Block inner, 10MHz to 40GHz VSWR1.3, rated 50 Volt in Stainless Steel SD8267

URL: https://www.fairviewmicrowave.com/dc-block-10-mhz-40-ghz-2.92mm-connectors-sd8267-p.aspx







