



# 50 ohm BNC plug to TNC jack DC Block inner from 10MHz to 3GHz rated 100 Volt in Brass

Fairview Microwave SD8282 is an inner DC block with BNC/TNC connectors. It has a blocking capacitor on the inner conductor and operates from 10 MHz to 3 GHz. Our BNC/TNC DC block offers good insertion loss of 0.2 dB and has a maximum operating voltage of 100 Vdc. DC blocks are commonly used to filter out unwanted DC signals, while allowing AC drive signals to pass through. They can help improve signal to noise ratio (SNR), eliminate ground loops, or provide isolation in your test setup. All of Fairview Microwave DC blocks are in stock and available to ship same-day.

## **Electrical Specifications**

Description	Min	Тур	Max	Units
Frequency Range	0.01		3	GHz
Impedance		50		Ohms
VSWR			1.2:1	
Insertion Loss			0.2	dB
Operating Voltage (DC)			100	Volts

## **Mechanical Specifications**

Size	
Length	2.08 in [52.83 mm]
Width	0.571 in [14.5 mm]
Height	0.571 in [14.5 mm]
Weight	0.1 lbs [45.36 g]

Housing Material and Plating Brass, Tri-Metal

Configuration

Package Type

Description	Connector 1	Connector 2	
Туре	BNC Male	TNC Female	
Inner Cond Material & Platin	g Bronze, Gold	Bronze, Gold	

Connectorized

**Compliance Certifications** (see product page for current document)

#### **Plotted and Other Data**

Notes:



### **Features:**

- Inner DC Blocks with Brass Body
- BNC (M) to TNC (F) between series connectorized configuration
- Operates from 10 MHz to 3 GHz
- 50 Ohm Impedance

# **Applications:**

- Test & Measurement
- Ground Loop Elimination
- Signal to Noise Ratio (SNR) Improvement

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





50 ohm BNC plug to TNC jack DC Block inner from 10MHz to 3GHz rated 100 Volt in Brass from Fairview Microwave is instock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

Click the following link to obtain additional part information: 50 ohm BNC plug to TNC jack DC Block inner from 10MHz to 3GHz rated 100 Volt in Brass SD8282

URL: https://www.fairviewmicrowave.com/dc-block-10-mhz-3-ghz-bnc-connectors-sd8282-p.aspx







