

SM2035 DATA SHEET

SMA Female to SMC Plug Adapter

SMA female to SMC plug adapter part number SM2035 from Fairview Microwave is in-stock and ships same day. This Fairview SMA to SMC adapter has a female to plug gender configuration. SM2035 SMA female to SMC plug adapter operates to 10 GHz. The Fairview Microwave RF adapter provides excellent VSWR of 1.2:1 maximum. The SMA connector mates mechanically with commercially available 3.5mm and 2.92mm (K) connectors.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		10	GHz
VSWR			1.2:1	

Electrical Specification Notes: Values at 25°C, sea level.

Mechanical Specifications

Size Length Width Weight		0.647 in [16.43 mm] 0.25 in [6.35 mm] 0.00529 lbs [2.4 g]	
Description	Connector 1	Connector 2	
Туре	SMA Female	SMC Plug	
Polarity	Standard	Standard	
Interface Specification	MIL-STD-348	MIL-STD-348	
Hex Size		1/4 inch	



Configuration:

- SMA Female Connector 1
- SMC Plug Connector 2
- 50 Ohm
- Straight Body Geometry

Features:

- VSWR of 1.2:1 max up to 10 GHz
- SMA interface meets MIL-STD-348
- SMC interface meets MIL-STD-348
- Contact plating according to MIL-G-45204
- Gold Plated Contact

Applications:

- Enables Between Series
 Connections
- General Purpose Test

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Material Specifications

Description	Connector 1	Connector	2
Туре	SMA Female	SMC Plug	
Contact Material	Beryllium Copper	Beryllium Cop	oper
Contact Plating	Gold	Gold	
Contact Plating Spec.	MIL-G-45204	MIL-G-4520)4
Insulation Material	PTFE	PTFE	
Outer Contact Material	Brass		
Outer Contact Plating	Nickel		
Outer Contact Plating Spec.	QQ-N-290		
Body Material		Brass	
Body Plating		Nickel	
Body Plating Spec.		QQ-N-290)
Coupling Nut Material		Brass	
Coupling Nut Plating		Nickel	
Coupling Nut Plating Spec.		QQ-N-290)

Environmental Specifications

Temperature Operating Range

-65 to +165 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Typical Performance Data







SMA Female to SMC Plug Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order


For additional information on this product, please click the following link: SMA Female to SMC Plug Adapter SM2035

URL: https://www.fairviewmicrowave.com/sma-female-smc-plug-adapter-sm2035-p.aspx

to implement improvements. Fairview Microwave ceserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.







*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

X ±0.2 XX ±0.1 .XXX ±0.05

FAIRVIEW MICROWAVE INC.	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].				NY TIME.	
SMA Female to SMC Plug Adapter	DWG NO SM2035		CAGE CODE 3FKR5			
	CAD FILE 092716	SHEET	SCAL	E N/A	SIZE A	2233

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689