

SSMB Jack to SSMB Jack Bulkhead Adapter

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		12	GHz
VSWR			1.45:1	

Mechanical Specifications

Size		
Length		0.623 in [15.82 mm]
Width		0.154 in [3.91 mm]
Weight		0.00176 lbs [0.8 g]

Description	Connector 1	Connector 2
Type	SSMB Jack	SSMB Jack
Connection Method	Standard	Standard
Polarity	Standard	Standard

Material Specifications

Description	Connector 1	Connector 2
Type	SSMB Jack	SSMB Jack
Contact Material	Beryllium Copper	Beryllium Copper
Contact Plating	Gold	Gold
Contact Plating Spec.	MIL-G-45204	MIL-G-45204
Insulation Material	PTFE	PTFE
Body Material	Brass	Brass

Environmental Specifications

Temperature	
Operating Range	-55 to +125 deg C

Compliance Certifications (visit www.FairviewMicrowave.com for current document)

RoHS Compliant	
REACH Compliant	12/17/2015

Plotted and Other Data

Notes:




Configuration:

- SSMB Jack Connector 1
- SSMB Jack Connector 2
- 50 Ohms
- Straight Body Geometry
- Bulkhead Mount Method

Fairview Microwave
 1130 Junction Dr. #100
 Allen, TX 75013
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Typical Performance Data




SSMB Jack to SSMB Jack Bulkhead Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [SSMB Jack to SSMB Jack Bulkhead Adapter SM2171](#)

URL: <https://www.fairviewmicrowave.com/mini-smb-jack-mini-smb-jack-bulkhead-adapter-sm2171-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



**RECOMMENDED
 MOUNTING HOLE**

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE SSMB Jack to SSMB Jack Bulkhead Adapter		DWG NO SM2171		CAGE CODE 3FKR5	
CAD FILE	072116	SHEET	SCALE	N/A	SIZE A 5568