

# SM3402 DATA SHEET

# **BNC Female to RP BNC Male Adapter**

BNC female to RP BNC male adapter part number SM3402 from Fairview Microwave is in-stock and ships same day. This Fairview BNC to reverse polarity BNC adapter has a female to male gender configuration. SM3402 BNC female to reverse polarity BNC male adapter operates to 4 GHz. The Fairview Microwave RF adapter provides excellent VSWR of 1.25:1 maximum.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

#### **Electrical Specifications**

Description	Min	Тур	Max	Units
Frequency Range	DC		4	GHz
VSWR			1.25:1	

Electrical Specification Notes: Values at 25°C, sea level.

#### **Mechanical Specifications**

	1.22 in [30.99 mm]
	0.03263 lbs [14.8 g]
Connector 1	Connector 2
BNC Female	BNC Male
Standard	Reverse Polarity
MIL-STD-348	8 MIL-STD-348
	BNC Female Standard



### **Configuration:**

- BNC Female Connector 1
- BNC Male Reverse Polarity Connector 2
- •50 Ohm
- Straight Body Geometry

### **Features:**

- VSWR of 1.25:1 max up to 4 GHz
- BNC interface meets MIL-STD-348
- Contact plating according to MIL-G-45204
- Gold Plated Contact

## **Applications:**

General Purpose Test

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





#### **Material Specifications**

Description	Connector 1	Connector 2
Туре	BNC Female	BNC Male
Contact Plating	Gold	Gold
Contact Plating Spec.	MIL-G-45204	MIL-G-45204
Outer Contact Material	Brass	
Outer Contact Plating	Nickel	
Outer Contact Plating Spec.	QQ-N-290	
Body Material		Brass
Body Plating		Nickel
Body Plating Spec.		QQ-N-290
Coupling Nut Material		Brass
Coupling Nut Plating		Nickel
Coupling Nut Plating Spec.		QQ-N-290

### **Environmental Specifications**

**Temperature** Operating Range


-65 to +165 deg C

Compliance Certifications (see product page for current document)

#### **Plotted and Other Data**

Notes:

#### **Typical Performance Data**



1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





BNC Female to RP BNC Male Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/ microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

The information contained in this document is accurate to the best of our knowledge and representative of the part

For additional information on this product, please click the following link: BNC Female to RP BNC Male Adapter SM3402


URL: https://www.fairviewmicrowave.com/bnc-female-rp-bnc-male-adapter-sm3402-p.aspx

described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







STANDARD TOLERANCES .X ±0.2 .XX ±0.1 .XXX ±0.05

\*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC.	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
BNC Female to RP BNC Male Adapter	DWG NO SM3402		CAGE CODE 3FKR5			
	CAD FILE 102416	SHEET	SCAL	E N/A	SIZE A	2233

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689