

SM3528 DATA SHEET

BNC Female to N Female Adapter

BNC female to type N female adapter part number SM3528 from Fairview Microwave is in-stock and ships same day. This Fairview BNC to type N adapter has a female to female gender configuration. SM3528 BNC female to type N female adapter operates to 4 GHz. The Fairview Microwave RF adapter provides good VSWR of 1.5:1 maximum.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connnector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Min	Тур	Мах	Units
Frequency Range	DC		4	GHz
VSWR			1.5:1	
Operating Voltage (AC)			500	Vrms
DWV (AC)			1,500	Vrms
Inner Conductor DC Resistance	e		1.5	mOhms
Outer Conductor DC Resistand	ce		1	mOhms
Insulation Resistance	5,000			MOhms

Electrical Specification Notes: Values at 25°C, sea level.

Mechanical Specifications

Size Length Width	1.102 in [27.99 mm] 0.61 in [15.49 mm]
Weight	0.04277 lbs [19.4 g]

Description	Connector 1	Connector 2		
Туре	BNC Female	N Female		
Polarity	Standard	Standard		
Interface Specification	MIL-STD-348A	MIL-STD-348A		
Mating Cycles	500	500		



Configuration:

- BNC Female Connector 1
- N Female Connector 2
- 50 Ohms
- Straight Body Geometry

Features:

- VSWR of 1.5:1 max up to 4 GHz
- BNC interface meets MIL-STD-348A
- N interface meets MIL-STD-348A
- 30 µin minimum contact plating
- Gold Plated Beryllium Copper Contact

Applications:

- Enables Between Series
 Connections
- General Purpose Test

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Material Specifications

Description	Connector 1	Connector 2
Туре	BNC Female	N Female
Contact Material	Beryllium Copper	Beryllium Copper
Contact Plating	Gold	Gold
Contact Plating Spec.	30 µin minimum	30 µin minimum
Insulation Material	PTFE	PTFE
Outer Contact Material	Brass	Brass
Outer Contact Plating	Nickel	Nickel
Outer Contact Plating Spec.	100 µin minimum	100 µin minimum

Environmental Specifications

Temperature Operating Range Vibration Salt Spray

-65 to +165 deg C MIL-STD-202, Method 204, Condition D MIL-STD-202, Method 101, Condition B

Compliance Certifications (see product page for current document)

Plotted and Other Data


Notes:











Typical Performance Data

BNC Female to N Female Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: BNC Female to N Female Adapter SM3528


URL: https://www.fairviewmicrowave.com/bnc-female-n-female-adapter-sm3528-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







FAIRVIEW MICROWAVE INC.	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
BNC Female to N Female Adapter	DWG NO SM3528			CAGE CODE 3FKR5		
	CAD FILE 111815	SHEET	SCAL	E N/A	SIZE A	150

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689