



Mini SMP Female to 2.92mm Male Cable RG-405 Coax and RoHS Compliant

Electrical Specifications

Description	Min	Тур	Max	Units	
Frequency Range	DC		26.5	GHz	
VSWR			1.35:1		

Mechanical Specifications

Cable Assembly

Cable Type Impedance Dielectric Type

RG-405 50 Ohms PTFE

Connectors

Description	Connector 1	Connector 2
Туре	Mini SMP Femal	e 2.92mm Male
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material & Plating	Beryllium Copper, G	Gold Brass
Coupling Nut Material & Pla	iting	Passivated Stainless Steel
Torque		9 in-lbs [1.02 Nm]
Body Material & Plating	Gold	Passivated Stainless Steel

Environmental Specifications

Compliance Certifications (visit www.FairviewMicrowave.com for current

document)

RoHS Compliant Yes

Plotted and Other Data

Notes:



Configuration:

- Mini SMP Female
- 2.92mm Male
- RG-405

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com




SCA76086-12 = 12 inches long cable SCA76086-100cm = 100 cm long cable



- Length

Typical Performance Data

Example:




Mini SMP Female to 2.92mm Male Cable RG-405 Coax and RoHS Compliant from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: Mini SMP Female to 2.92mm Male Cable RG-405 Coax and RoHS Compliant SCA76086

URL: http://www.fairviewmicrowave.com/mini-smp-female-2.92mm-male-cable-rg-405-coax-sca76086-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
Mini SMP Female to 2.92mm Male Cable RG-405 Coax and RoHS Compliant	DWG NO SCA76086			CAGE CODE 3FKR5		
	CAD FILE 102215	SHEET	SCALE	E N/A	SIZE A	5568