



SMB Jack to SMB Jack Bulkhead Adapter

SMB jack to SMB jack bulkhead adapter part number SM2002 from Fairview Microwave is in-stock and ships same day. This Fairview SMB to SMB adapter has a jack to jack gender configuration. SM2002 SMB jack to SMB jack adapter operates to 4 GHz. Our RF SMB to SMB bulkhead adapter allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications. The Fairview Microwave RF adapter provides good VSWR of 1.3:1 maximum.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Min	Тур	Max	Units		
Frequency Range	DC		4	GHz		
VSWR			1.3:1			
Operating Voltage (AC)			335	Vrms		

Electrical Specification Notes:

Values at 25°C, sea level.

Mechanical Specifications

chamear Speemeati	0113
Size	
Length	
Width	
Height	
Weight	

0.724 in [18.39 mm] 0.195 in [4.95 mm] 0.25 in [6.35 mm] 0.00309 lbs [1.4 g]

Description	Connector 1	Connector 2		
Туре	SMB Jack	SMB Jack		
Polarity	Standard	Standard		
Interface Specification	MIL-STD-348A	MIL-STD-348A		



Configuration:

- SMB Jack Connector 1
- SMB Jack Connector 2
- 50 Ohms
- Straight Body Geometry
- Bulkhead Mount Method

Features:

- VSWR of 1.3:1 max up to 4 GHz
- SMB interface meets MIL-STD-348A
- 30 µin minimum contact plating
- Gold Plated Brass Contact

Applications:

- General Purpose Test
- Rack Mounted Equipment

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Material Specifications

Description	Connector 1	Connector 2			
Туре	SMB Jack	SMB Jack			
Contact Material	Brass	Brass			
Contact Plating	Gold	Gold			
Contact Plating Spec.	30 μin minimum	30 µin minimum			
Insulation Material	PTFE	PTFE			
Outer Contact Material	Brass	Brass			
Outer Contact Plating	Gold	Gold			
Outer Contact Plating Spec.	3 µin minimum	3 µin minimum			

Environmental Specifications

Temperature

Operating Range


-65 to +165 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Typical Performance Data







SMB Jack to SMB Jack Bulkhead Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: SMB Jack to SMB Jack Bulkhead Adapter SM2002

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order

URL: https://www.fairviewmicrowave.com/smb-jack-smb-jack-bulkhead-adapter-sm2002-p.aspx

	nent improv												
stated, al	l specificati	ons are i	nominal.	Fairvie	w Microwa	ve does n	ot make	any rep	resentat	ion or v	warranty re	gard	ing the
suitability	of the part	t describ	ed hereir	for any	/ particulai	purpose,	and Fair	view Mi	crowave	does n	ot assume	any	liability
arising ou	t of the use	of any p	part or do	cument	ation.								





FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].						
SMB Jack to SMB Jack Bulkhead Adapter	DWG NO SM2002				AGE CODE 3FKR5		
	CAD FILE 011216	SHEET	SCALE	E N/A	SIZE A	5568	