

## SM4407 DATA SHEET

# Bulkhead 4.1/9.5 Mini DIN Female to 4.1/9.5 Mini DIN Female Adapter IP67 Mated

Bulkhead 4.1/9.5 Mini DIN female to 4.1/9.5 Mini DIN female adapter part number SM4407 from Fairview Microwave is in-stock and ships same day. This Fairview 4.1/9.5 Mini DIN to 4.1/9.5 Mini DIN adapter has a female to female gender configuration. SM4407 4.1/9.5 Mini DIN female to 4.1/9.5 Mini DIN female adapter operates to 6 GHz. The Fairview Microwave RF adapter provides excellent VSWR of 1.25:1 maximum. Our RF 4.1/9.5 Mini DIN bulkhead to 4.1/9.5 Mini DIN adapter allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

### **Electrical Specifications**

Description	Min	Тур	Max	Units	
Frequency Range	DC		6	GHz	
VSWR			1.25:1		

#### **Specifications by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC to 3	3 to 6				GHz
VSWR, Max	1.1:1	1.25:1				

Electrical Specification Notes: Values at 25°C, sea level.

#### **Mechanical Specifications**

•	7	$\boldsymbol{\mathcal{L}}$

 Length
 1.6 in [40.64 mm]

 Width
 0.98 in [24.89 mm]

 Weight
 0.1845 lbs [83.69 g]

Description	Connector 1	Connector 2
Туре	4.1/9.5 Mini DIN Female 4	.1/9.5 Mini DIN Female
Polarity	Standard	Standard
Mating Cycles	500	500



## **Configuration:**

- 4.1/9.5 Mini DIN Female Connector 1
- 4.1/9.5 Mini DIN Female Connector 2
- 50 Ohm
- Straight Body Geometry
- Bulkhead Mount Method

#### **Features:**

- VSWR of 1.25:1 max up to 6 GHz
- Rated IP67 Mated
- Silver Plated Contact

## **Applications:**

- General Purpose Test
- Rack Mounted Equipment

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





#### **Material Specifications**

Description	Connector 1	Connector 2		
Туре	4.1/9.5 Mini DIN Female	4.1/9.5 Mini DIN Female		
Contact Material	Beryllium Copper	Beryllium Copper		
Contact Plating	Silver	Silver		
Insulation Material	PTFE	PTFE		
Outer Contact Material	Brass	Brass		
Outer Contact Plating	Tri-Metal	Tri-Metal		

## **Environmental Specifications**

**Temperature** 

Operating Range
Ingress Protection (IP) Rating


-55 to +120 deg C IP67 Mated

**Compliance Certifications** (see product page for current document)

#### **Plotted and Other Data**

Notes:

#### **Typical Performance Data**







Bulkhead 4.1/9.5 Mini DIN Female to 4.1/9.5 Mini DIN Female Adapter IP67 Mated from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: Bulkhead 4.1/9.5 Mini DIN Female to 4.1/9.5 Mini DIN Female Adapter IP67 Mated SM4407

URL: https://www.fairviewmicrowave.com/bulkhead-4.1-9.5-mini-din-female-4.1-9.5-mini-din-female-adapter-sm4407-p. aspx









FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
Bulkhead 4.1/9.5 Mini DIN Female to 4.1/9.5 Mini DIN	DWG NO	SM4407		CAGE CODE 3FKR5		
Female Adapter IP67 Mated	CAD FILE 062014	SHEET	SCALE	E N/A	SIZE A	2233