

SM4417 DATA SHEET

7/16 DIN Male to 4.1/9.5 Mini DIN Female Adapter IP67 Mated

Electrical Specifications

Frequency Range DC to 6 GHz
Maximum VSWR 1.25:1
Maximum Passive Intermodulation (2 x 20 Watts) 160 dBc

Mechanical Specifications

Size

Length Width Weight

Connector 1

Type Inner Conductor Material and Plating Coupling Nut Material and Plating

Hex Size Torque

Body Material and Plating

Dielectric Type

Connector 2

Type Inner Conductor Material and Plating Body Material and Plating

Dielectric Type

Environmental Specifications Temperature

Operating Range

operating nange

Ingress Protection

1.809 in [45.95 mm] 1.25 in [31.75 mm]

0.259 lbs [117.48 g]

7/16 DIN Male Beryllium Copper, Silver Brass, Tri-Metal 32 mm 18.333 ft-lbs [24.86 Nm]

Brass, Tri-Metal

PTFE

4.1/9.5 Mini DIN Female Beryllium Copper, Silver Brass, Tri-Metal

PTFE

-40 to +120 deg C

IP67 Mated

Compliance Certifications (visit www.FairviewMicrowave.com for current

document)

RoHS Compliant Yes

Plotted and Other Data

Notes:

· Values at 25 °C, sea level



Features:

- Ingress Protection: IP67 Mated
- Connector 1: 7/16 DIN Male
- Impedance 1: 50 Ohms
- Connector 2: 4.1/9.5 Mini DIN Female
- Impedance 2: 50 Ohms
- Adapter Design: Standard
- Body Style: Straight
- Low PIM: 160 dBc


Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com



Typical Performance Data



7/16 DIN Male to 4.1/9.5 Mini DIN Female Adapter IP67 Mated from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: 7/16 DIN Male to 4.1/9.5 Mini DIN Female Adapter IP67 Mated SM4417

URL: http://www.fairviewmicrowave.com/7-16-male-4.1-9.5-mini-din-female-adapter-sm4417-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
7/16 DIN Male to 4.1/9.5 Mini DIN Female Adapter IP67 Mated	DWG NO SM4417			CAGE CODE 3FKR5		
	CAD FILE 061014	SHEET	SCALE	N/A	SIZE A	2233