



N Female to SC Female Adapter

Type N female to SC female adapter part number SM4651 from Fairview Microwave is in-stock and ships same day. This Fairview type N to SC adapter has a female to female gender configuration. SM4651 type N female to SC female adapter operates to 11 GHz. The Fairview Microwave RF adapter provides excellent VSWR of 1.25:1 maximum.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		11	GHz
VSWR			1.25:1	

Electrical Specification Notes: Values at 25°C, sea level.

Mechanical Specifications

Size	
Length	
Width	

Weight

1.712 in [43.5 mm] 0.695 in [17.65 mm] 0.1265 lbs [57.38 g]

Description	Connector 1	Connector 2	
Туре	N Female	SC Female	
Polarity	Standard	Standard	
Interface Specification	MIL-STD-348	MIL-STD-348	

Material Specifications

Description	Connector 1	Connector 2		
Туре	N Female	SC Female		
Contact Material	Beryllium Copper	Beryllium Copper		
Contact Plating	Silver	Silver		
Contact Plating Spec.	QQ-S-365	QQ-S-365		
Insulation Material	PTFE	PTFE		
Outer Contact Material	Brass	Brass		
Outer Contact Plating	Nickel	Nickel		
Outer Contact Plating Spec.	QQ-N-290	QQ-N-290		



Configuration:

- N Female Connector 1
- SC Female Connector 2
- 50 Ohm
- Straight Body Geometry

Features:

- VSWR of 1.25:1 max up to 11 GHz
- Type N interface meets MIL-STD-348
- SC interface meets MIL-STD-348
- Contact plating according to QQ-S-365
- Silver Plated Beryllium Copper Contact

Applications:

- Enables Between Series Connections
- General Purpose Test

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Environmental Specifications

Temperature


Operating Range -65 to +165 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Typical Performance Data



N Female to SC Female Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: N Female to SC Female Adapter SM4651

URL: https://www.fairviewmicrowave.com/n-female-sc-female-adapter-sm4651-p.aspx


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2020







STANDARD TOLERANCES

.X ±0.2

.XX ±0.01

.XXX ±0.005

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC. www.fairviewmicrowave.com	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
N Female to SC Female Adapter	DWG NO SM4651			CAGE CODE 3FKR5		
	CAD FILE 093016	SHEET	SCAL	LE N/A SIZE A		41742