

SM4730 DATA SHEET

RA SMA Female to TNC Male Adapter

RA SMA female to TNC male adapter part number SM4730 from Fairview Microwave is in-stock and ships same day. This Fairview SMA to TNC adapter has a female to male gender configuration. SM4730 SMA female to TNC male adapter operates to 6 GHz. The SMA connector mates mechanically with commercially available 3.5mm and 2.92mm (K) connectors. This low profile right angle SMA to TNC adapter allows for easier connections in tight spaces. The Fairview Microwave RF adapter provides excellent VSWR of 1.2:1 maximum.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Min	Тур	Max	Units
DC		6	GHz
		1.2:1	
		-77	DC 6

Electrical Specification Notes: Values at 25° C, sea level.

Mechanical Specifications

Size	
Length	0.96 in [24.38 mm]
Weight	0.0485 lbs [22 g]

Description	Connector 1	Connector 2		
Туре	SMA Female	TNC Male		
Polarity	Standard	Standard		
Interface Specification	MIL-STD-348	MIL-STD-348		
Mating Cycles	500	500		
Hex Size		9/16 inch		



Configuration:

- SMA Female Connector 1
- TNC Male Connector 2
- 50 Ohms
- Right Angle Body Geometry

Features:

- VSWR of 1.2:1 max up to 6 GHz
- SMA interface meets MIL-STD-348
- TNC interface meets MIL-STD-348
- Contact plating according to MIL-G-45204
- Gold Plated Beryllium Copper Contact

Applications:

- Enables Between Series Connections
- General Purpose Test

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com





Material Specifications

Description	Connector 1	Connector 2		
Туре	SMA Female	TNC Male		
Contact Material	Beryllium Copper	Beryllium Copper		
Contact Plating	Gold	Gold		
Contact Plating Spec.	MIL-G-45204	MIL-G-45204		
Insulation Material	PTFE	PTFE		
Outer Contact Material	Passivated Stainless Steel			
Body Material		Brass		
Body Plating		Nickel		
Body Plating Spec.		QQ-N-290		

Environmental Specifications

Temperature

Operating Range


-55 to +125 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Typical Performance Data







RA SMA Female to TNC Male Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order

For additional information on this product, please click the following link: RA SMA Female to TNC Male Adapter SM4730

URL: https://www.fairviewmicrowave.com/ra-sma-female-tnc-male-adapter-sm4730-p.aspx

to implem	nent improve	ments. Fairview	Microwa	ave reserve	es the righ	nt to mak	e such	changes a	as require	d. Unless	otherwise
stated, al	l specification	ns are nominal.	Fairvie	w Microwa	ve does n	ot make	any rep	resentati	on or war	ranty rega	arding the
suitability	of the part	described hereir	for any	, particular	purpose,	and Fair	view Mi	crowave	does not	assume ai	ny liability
arising ou	t of the use	of any part or do	ocument	ation.							





FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].						
RA SMA Female to TNC Male Adapter	DWG NO CAGE CODE 3FKI					FKR5	
	CAD FILE 061815	SHEET	SCALE	N/A	SIZE A	5568	