

# SM4776 DATA SHEET

## **MMCX Jack to SMA Female Adapter**

MMCX jack to SMA female adapter part number SM4776 from Fairview Microwave is in-stock and ships same day. This Fairview MMCX to SMA adapter has a jack to female gender configuration. SM4776 MMCX jack to SMA female adapter operates to 6 GHz. The Fairview Microwave RF adapter provides excellent VSWR of 1.25:1 maximum.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connnector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

### **Electrical Specifications**

Description	Min	Тур	Max	Units
Frequency Range	DC		6	GHz
VSWR			1.25:1	
Operating Voltage (AC)			250	Vrms

Electrical Specification Notes: Values at 25°C, sea level.

### **Mechanical Specifications**

<b>Size</b> Length Width Weight		0.846 in [21.49 mm] 0.354 in [8.99 mm] 0.0105 lbs [4.76 g]
Description	Connector 1	Connector 2
Туре	MMCX Jack	SMA Female
Polarity	Standard	Standard
Interface Specification	MIL-STD-348A	MIL-STD-348A
Mating Cycles	500	500

#### **Material Specifications**

Description	Connector 1	Connector 2	
Туре	MMCX Jack	SMA Female	
Contact Material	Beryllium Copper	Beryllium Copper	
Contact Plating	Gold	Gold	
Contact Plating Spec.	50 µin minimum	50 µin minimum	
Insulation Material	PTFE	PTFE	
Outer Contact Material	Brass	Brass	
Outer Contact Plating	Gold	Gold	
Outer Contact Plating Spec.	3 µin minimum	3 µin minimum	



### **Configuration:**

- MMCX Jack Connector 1
- SMA Female Connector 2
- 50 Ohms
- Straight Body Geometry

### **Features:**

- VSWR of 1.25:1 max up to 6 GHz
- MMCX interface meets MIL-STD-348A
- SMA interface meets MIL-STD-348A
- 50 µin minimum contact plating
- Gold Plated Beryllium Copper Contact

### **Applications:**

- Enables Between Series
  Connections
- General Purpose Test

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





### **Environmental Specifications**

**Temperature** Operating Range


-55 to +155 deg C

### Compliance Certifications (see product page for current document)

#### **Plotted and Other Data**

Notes:

### **Typical Performance Data**



MMCX Jack to SMA Female Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/ microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: MMCX Jack to SMA Female Adapter SM4776

URL: https://www.fairviewmicrowave.com/mmcx-jack-sma-female-adapter-sm4776-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.







STANDARD TOLERANCES .X ±0.2 .XX ±0.1 .XXX ±0.05

\*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC.	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
MMCX Jack to SMA Female Adapter	DWG NO SM4776		CAGE CODE 3FKR5			
	CAD FILE 122215	SHEET	SCAL	E N/A	SIZE A	150

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689