



RA 2.92mm Female to 3.5mm Male Adapter

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		34.5	GHz
VSWR			1.3:1	
Return Loss			17.7	dB

Mechanical Specifications

Weight 0.01235 lbs [5.6 g]

Description	Connector 1	Connector 2
Туре	2.92mm Female 3.5mm Mal	
Connection Method	Standard Standard	
Polarity	Standard	Standard
Hex Size	5/16 Inch	
Mating Torque		9 in-lbs max
		[1.02 Nm] max

Material Specifications

Description	Connector 1	Connector 2	
Туре	2.92mm Female	3.5mm Male	
Contact Material	Beryllium Copper	Beryllium Copper	
Contact Plating	Gold	Gold	
Contact Plating Spec.	MIL-G-45204	MIL-G-45204	
Insulation Material	Air	Air	
Outer Contact Material	Passivated Stainless Stee	el .	
Outer Contact Plating Spec.	ASTM A380		
Body Material	Passivated Stainless Stee	Passivated Stainless Steel	
Body Plating Spec.	ASTM A380	ASTM A380	
Coupling Nut Material		Passivated Stainless Steel	
Coupling Nut Plating Spec.		ASTM A380	

Environmental Specifications

Temperature

Operating Range -55 to +125 deg C

Compliance Certifications (visit www.FairviewMicrowave.com for current document)

RoHS Compliant

REACH Compliant 12/17/2015

Plotted and Other Data

Notes:



Configuration:


- 2.92mm Female Connector 1
- 3.5mm Male Connector 2
- 50 Ohms
- Right Angle Body Geometry

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com



Typical Performance Data



RA 2.92mm Female to 3.5mm Male Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: RA 2.92mm Female to 3.5mm Male Adapter SM3261

URL: http://www.fairviewmicrowave.com/ra-2.92mm-female-3.5mm-male-adapter-sm3261-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
RA 2.92mm Female to 3.5mm Male Adapter	DWG NO SM3261			CAGE CODE 3FKR5		
	CAD FILE 030314	SHEET	SCALE	≣ N/A	SIZE A	2233