



RA 3.5mm Female to 3.5mm Female Adapter

Electrical Specifications

Frequency Range DC to 34.5 GHz
Maximum VSWR 1.25:1
Maximum Insertion Loss 0.3 dB



Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Range	DC to 0	0 to 34.5				GHz
VSWR	1.25:1					
Return Loss	19.085					dB

Mechanical Specifications

Connector 1

Color

Type
Inner Conductor Material and Plating
Inner Conductor Plating Specification
Outer Conductor Material and Plating
Outer Conductor Plating Specification
Body Material and Plating
Body Plating Specification
Dielectric Type

Connector 2

Type
Inner Conductor Material and Plating
Inner Conductor Plating Specification
Outer Conductor Material and Plating
Outer Conductor Plating Specification
Body Material and Plating
Body Plating Specification
Dielectric Type

Silver

3.5mm Female

MIL-G-45204

ASTM A380

ASTM A380

Air

Air

Beryllium Copper, Gold

Passivated Stainless Steel

Passivated Stainless Steel

3.5mm Female
Beryllium Copper, Gold
MIL-G-45204
Passivated Stainless Steel
ASTM A380
Passivated Stainless Steel
ASTM A380

Environmental Specifications Temperature

Operating Range -55 to +125 deg C

Compliance Certifications (visit www.FairviewMicrowave.com for current document)

RoHS Compliant Yes

Plotted and Other Data

Notes:

• Values at 25 °C, sea level

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com

Features:

Connector 1: 3.5mm Female
Impedance 1: 50 Ohms
Connector 2: 3.5mm Female
Impedance 2: 50 Ohms
Adapter Design: Standard





RA 3.5mm Female to 3.5mm Female Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: RA 3.5mm Female to 3.5mm Female Adapter SM3302

URL: http://www.fairviewmicrowave.com/ra-3.5mm-female-3.5mm-female-adapter-sm3302-p.aspx









FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
RAE3.5mm Female to 3.5mm Female Adapter 3.5mm Female to 3.5mm Female Right Angle	DWG NO SM3302			CAGE CODE 3FKR5		
Adapter	CAD FILE 030314	SHEET	SCALE	N/A	SIZE A	2233