

# SM3505 DATA SHEET

## N Female to BNC Female Bulkhead Adapter

Type N female to BNC female bulkhead adapter part number SM3505 from Fairview Microwave is in-stock and ships same day. This Fairview type N to BNC adapter has a female to female gender configuration. SM3505 type N female to BNC female adapter operates to 4 GHz. The Fairview Microwave RF adapter provides good VSWR of 1.35:1 maximum. Our RF type N to BNC bulkhead adapter allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

### **Electrical Specifications**

| Description     | Min | Тур | Мах    | Units |
|-----------------|-----|-----|--------|-------|
| Frequency Range | DC  |     | 4      | GHz   |
| VSWR            |     |     | 1.35:1 |       |

#### Specifications by Frequency

| Description     | F1      | F2     | F3 | F4 | F5 | Units |
|-----------------|---------|--------|----|----|----|-------|
| Frequency Range | DC to 2 | 2 to 4 |    |    |    | GHz   |
| VSWR, Max       | 1.2:1   | 1.35:1 |    |    |    |       |

Electrical Specification Notes: Values at 25°C, sea level.

#### **Mechanical Specifications**

| 1.75 in [44.45 mm] |  |  |  |
|--------------------|--|--|--|
| 0.112 lbs [50.8 g] |  |  |  |
| N Female           | BNC Female                                 |  |  |
| Standard           | Standard                                   |  |  |
| MIL-STD-348        | MIL-STD-348                                |  |  |
|                    | 0.1<br>Connector 1<br>N Female<br>Standard |  |  |



## **Configuration:**

- N Female Connector 1
- BNC Female Connector 2
- •50 Ohm
- Straight Body Geometry
- Bulkhead Mount Method

## **Features:**

- VSWR of 1.35:1 max up to 4 GHz
- Type N interface meets MIL-STD-348
- BNC interface meets MIL-STD-348
- Contact plating according to QQ-S-365
- Silver Plated Beryllium Copper Contact

## **Applications:**

- Enables Between Series
  Connections
- General Purpose Test
- Rack Mounted Equipment

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





#### **Material Specifications**


| Description                 | Connector 1      | Connector 2      |  |  |
|-----------------------------|------------------|------------------|--|--|
| Туре                        | N Female         | BNC Female       |  |  |
| Contact Material            | Beryllium Copper | Beryllium Copper |  |  |
| Contact Plating             | Silver           | Silver           |  |  |
| Contact Plating Spec.       | QQ-S-365         | QQ-S-365         |  |  |
| Outer Contact Material      | Brass            | Brass            |  |  |
| Outer Contact Plating       | Nickel           | Nickel           |  |  |
| Outer Contact Plating Spec. | QQ-N-290         | QQ-N-290         |  |  |
|                             |                  |                  |  |  |

**Compliance Certifications** (see product page for current document)

## **Plotted and Other Data**

Notes:

#### **Typical Performance Data**



N Female to BNC Female Bulkhead Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: N Female to BNC Female Bulkhead Adapter SM3505


URL: https://www.fairviewmicrowave.com/n-female-bnc-female-bulkhead-adapter-sm3505-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







| ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM | UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  J. DIMENSIONS ARE IN INCHES [mm]. |       |                 |       |        |       |  |
|---|---|-------|-----------------|-------|--------|-------|--|
| N Female to BNC Female Bulkhead Adapter   | DWG NO SM3505   |       | CAGE CODE 3FKR5 |       |        |       |  |
|   | CAD FILE 101016   | SHEET | SCAL            | E N/A | SIZE A | 41742 |  |

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689