



Bulkhead N Female to BNC Female Adapter

Bulkhead type N female to BNC female adapter part number SM3506 from Fairview Microwave is in-stock and ships same day. This Fairview type N to BNC adapter has a female to female gender configuration. SM3506 type N female to BNC female adapter operates to 4 GHz. The Fairview Microwave RF adapter provides excellent VSWR of 1.2:1 maximum. Our RF type N bulkhead to BNC adapter allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		4	GHz
VSWR			1.2:1	
Operating Voltage (AC)			500	Vrms
DWV (AC)			1,500	Vrms
Insulation Resistance	5,000			MOhms

Electrical Specification Notes:

Values at 25°C, sea level.

Mechanical Specifications

Size Length Width Weight

1.5 in [38.1 mm] 0.531 in [13.49 mm] 0.09 lbs [40.82 g]

Description	Connector 1	Connector 2
Туре	N Female	BNC Female
Polarity	Standard	Standard
Interface Specification	MIL-STD-348	MIL-STD-348



Configuration:

- N Female Connector 1
- BNC Female Connector 2
- 50 Ohm
- Straight Body Geometry
- Bulkhead Mount Method

Features:

- VSWR of 1.2:1 max up to 4 GHz
- Type N interface meets MIL-STD-348
- BNC interface meets MIL-STD-348
- Contact plating according to MIL-G-45204
- · Gold Plated Contact

Applications:

- Enables Between Series Connections
- General Purpose Test
- · Rack Mounted Equipment

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (97

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Material Specifications

Connector 1	Connector 2		
N Female	BNC Female		
Beryllium Copper	Beryllium Copper		
Gold	Gold		
MIL-G-45204	MIL-G-45204		
Brass	Brass		
Nickel	Nickel		
QQ-N-290	QQ-N-290		
	N Female Beryllium Copper Gold MIL-G-45204 Brass Nickel		

Environmental Specifications

Temperature

Operating Range


-65 to +165 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Typical Performance Data







Bulkhead N Female to BNC Female Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: Bulkhead N Female to BNC Female Adapter SM3506


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order

URL: https://www.fairviewmicrowave.com/bulkhead-n-female-bnc-female-adapter-sm3506-p.aspx

to implem	nent impro	vements	. Fairview	/ Microv	vave reserv	ves the righ	nt to mak	ke such	changes	as req	juired. Unle	ss otl	herwise
											warranty r		
suitability	of the pa	t describ	oed hereir	n for an	y particula	ir purpose,	and Fair	rview M	icrowave	does	not assume	any	liability
arising ou	t of the us	e of any	part or do	ocumen	tation.								







STANDARD TOLERANCES
.X ±0.2

.X ±0.2 .XX ±0.1 .XXX ±0.05

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].							
Bulkhead N Female to BNC Female Adapter	DWG NO SM3506			CAGE CODE 3FKR5				
	CAD FILE 102106	SHEET	SCALE	N/A	SIZE A	41742		