

SM4245 DATA SHEET

Bulkhead Hermetically Sealed SMA Female to N Female Adapter

Bulkhead hermetically sealed SMA female to type N female adapter part number SM4245 from Fairview Microwave is in-stock and ships same day. This Fairview SMA to type N adapter has a female to female gender configuration. SM4245 SMA female to type N female adapter operates to 11 GHz. The SMA connector mates mechanically with commercially available 3.5mm and 2.92mm (K) connectors. Our RF SMA bulkhead to type N adapter allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications. The Fairview Microwave hermetic SMA to type N adapter prevents the leakage of gases, making it suitable for high pressure or vacuum applications or whenever an airtight seal is required. The Fairview Microwave RF adapter provides good VSWR of 1.3:1 maximum.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Min	Typ	May	Units
141111	ТУР	Max	Uilles
DC		11	GHz
		1.3:1	
		335	Vrms
		1,000	Vrms
5,000			MOhms
		DC	DC 11 1.3:1 335 1,000

Electrical Specification Notes: Values at 25° C, sea level.

Mechanical Specifications

Size

Length 1.232 in [31.29 mm]
Width 0.81 in [20.57 mm]
Weight 0.0776 lbs [35.2 g]

Description	Connector 1 Connector 2	
Туре	SMA Female	N Female
Polarity	Standard	Standard
Interface Specification	MIL-STD-348	MIL-STD-348
Connector Option	Hermetically Sealed	Hermetically Sealed

Mechanical Specification Notes:

The glass bead seal in the center of the adapter is sensitive to shock and axial pressure. If the adapter is subjected to shock and overtorquing of the coupling nut, the glass bead interseal will shatter easily. Jam nut torque not to exceed 15 inch pounds.



Configuration:

- SMA Female Connector 1
- N Female Connector 2
- 50 Ohms
- Straight Body Geometry
- Bulkhead Mount Method

Features:

- VSWR of 1.3:1 max up to 11 GHz
- Hermetically Sealed
- SMA interface meets MII-STD-348
- N interface meets MIL-STD-348
- Contact plating according to MIL-G-45204
- · Gold Plated Contact

Applications:

- Enables Between Series
 Connections
- · General Purpose Test
- Vacuum Test Environment
- Rack Mounted Equipment

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Material Specifications

Description	Description Connector 1	
Туре	SMA Female	N Female
Contact Plating	Gold	Gold
Contact Plating Spec.	MIL-G-45204	MIL-G-45204
Outer Contact Material	Passivated Stainless Steel	Passivated Stainless Steel

Environmental Specifications

Temperature


Operating Range Hermetic Seal -65 to +165 deg C Leak rate not to exceed 1x10^-7 cc/sec of helium at 1 atm differential

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Typical Performance Data








Bulkhead Hermetically Sealed SMA Female to N Female Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: Bulkhead Hermetically Sealed SMA Female to N Female Adapter SM4245

URL: https://www.fairviewmicrowave.com/bulkhead-hermetically-sealed-sma-female-n-female-adapter-sm4245-p.aspx







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].				
Bulkhead Hermetically Sealed SMA Female to N Female Adapter	DWG NO SM4245			CAGE CODE 3FKR5	
	CAD FILE 061815	SHEET	SCALE	N/A	SIZE A