

SM4419 DATA SHEET

7/16 DIN Female to 4.1/9.5 Mini DIN Male Adapter IP67 Mated

Electrical Specifications

Frequency Range DC to 6 GHz
Maximum VSWR 1.25:1
Maximum Insertion Loss 19.1 dB

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Range	DC to 3	3 to 6				GHz
VSWR	1.15:1	1.25:1				
Return Loss	23.1	19.1				dB

Mechanical Specifications

Size

Length 2.031 in [51.59 mm]
Weight 0.27117 lbs [123 g]

7/16 DIN Female

Brass, Tri-Metal

Brass, Tri-Metal

Brass, Tri-Metal

PTFF

22 mm

PTFE

Beryllium Copper, Silver

4.1/9.5 Mini DIN Male

90 in-lbs [10.17 Nm]

Beryllium Copper, Silver

Connector 1

Type Inner Conductor Material and Plating Body Material and Plating Dielectric Type

Connector 2

Type
Inner Conductor Material and Plating
Coupling Nut Material and Plating
Hex Size
Torque
Body Material and Plating
Dielectric Type

Environmental Specifications Temperature

Operating Range -40 to +120 deg C

Ingress Protection IP67 Mated

Compliance Certifications (visit www.FairviewMicrowave.com for current document)

Plotted and Other Data

Notes:

· Values at 25 °C, sea level



Features:


- Ingress Protection: IP67 MatedConnector 1: 7/16 DIN Female
- Impedance 1: 50 Ohms
- Connector 2: 4.1/9.5 Mini DIN Male
- Impedance 2: 50 OhmsAdapter Design: Standard
- Body Style: Straight

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com



Typical Performance Data




7/16 DIN Female to 4.1/9.5 Mini DIN Male Adapter IP67 Mated from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 7/16 DIN Female to 4.1/9.5 Mini DIN Male Adapter IP67 Mated SM4419

URL: http://www.fairviewmicrowave.com/7-16-female-4.1-9.5-mini-din-male-adapter-sm4419-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
7/16 DIN Female to 4.1/9.5 Mini DIN Male Adapter	DWG NO SM4419			CAGE CODE 3FKR5		
IP67 Mated	CAD FILE 061014	SHEET	SCALE	E N/A	SIZE A	2233