

# SM9974 DATA SHEET

# 2.4mm NMD Female to 2.92mm Female Adapter with Stainless Steel Body

2.4mm NMD female to 2.92mm female adapter part number SM9974 from Fairview Microwave is in-stock and ships same day. This Fairview 2.4mm NMD to 2.92mm adapter has a female to female gender configuration and is built of durable stainless steel. SM9974 2.4mm NMD female to 2.92mm female adapter operates to 40 GHz. The Fairview Microwave RF adapter provides excellent VSWR of 1.25:1 maximum.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

### **Electrical Specifications**

Description	Min	Тур	Max	Units
Frequency Range	DC		40	GHz
VSWR			1.25:1	
Operating Voltage (AC)			500	Vrms

#### **Mechanical Specifications**

#### Size

Length Width Height 1.440 in [36.6 mm] 0.75 in [19.05 mm] 0.75 in [19.05 mm]

Description	Connector 1	Connector 2	
Туре	2.4mm NMD Female	2.92mm Female	
Polarity	Standard	Standard	

#### **Material Specifications**

Description Connector 1		Connector 2	
Туре	2.4mm NMD Female	2.92mm Female	
Contact Material	Beryllium Copper	Beryllium Copper	
Contact Plating	Gold	Gold	
Contact Plating Spec.	4 µin minimum	4 μin minimum	
Body Material	Stainless Steel	Stainless Steel	
Body Plating	Passivated Stainless Steel	Passivated Stainless Steel	
Body Plating Spec.	100 µin minimum	100 μin minimum	

#### **Environmental Specifications**

#### Temperature

Operating Range

-65 to +165 deg C



# **Configuration:**

- 2.4mm NMD Female Connector 1
- 2.92mm Female Connector 2
- 50 Ohm
- Straight Body Geometry

#### **Features:**

- VSWR of 1.25:1 max up to 40 GHz
- 4 µin minimum contact plating
- Gold Plated Beryllium Copper Contact
- 30 µin min Gold Contact Plating

## **Applications:**

- Enables Between Series Connections
- General Purpose Test

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com

sales@fairviewmicrowave.com





**Compliance Certifications** (see product page for current document)

#### **Plotted and Other Data**

Notes:

2.4mm NMD Female to 2.92mm Female Adapter with Stainless Steel Body from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 2.4mm NMD Female to 2.92mm Female Adapter with Stainless Steel Body SM9974

URL: https://www.fairviewmicrowave.com/2.4mm-nmd-female-to-2.92mm-female-adapter-with-stainless-steel-body-sm9974-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





