

SMC292-0471 **DATA SHEET**

2.92mm Male Connector Clamp/Non-Solder Contact Attachment For .047 SR Cable

2.92mm male connector with clamp/non-solder contact attachment for .047 SR, part number SMC292-0471, from Fairview Microwave is in-stock and ships same day. This 2.92mm male connector operates up to a maximum frequency of 40 GHz and offers excellent VSWR of 1.25:1.

Fairview's 2.92mm male connector SMC292-0471 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		40	GHz
VSWR			1.25:1	

Mechanical Specifications

Size

Length 0.46 in [11.68 mm] Width/Dia. 0.312 in [7.92 mm]

Weight 0.0106 lbs [4.81 q] 500 Cycles

Mating Cycles

Material Specifications

Description	Material	Plating		
Contact	Beryllium Copper	Gold over Nickel 50 µin minimum		
Insulation	PEI			
Body	Passivated Stainless Steel	SAE-AMS-2700		
Coupling Nut	Passivated Stainless Steel	SAE-AMS-2700		

Environmental Specifications Temperature

Operating Range -55 to +100 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:



Configuration:

- 2.92mm Male Connector
- 50 Ohms
- Straight Body Geometry
- .047 SR Interface Type
- Clamp/Non-Solder Contact Attachment
- 5/16 inch Hex

Features:

- Operating Frequency of 40 GHz Max.
- Excellent VSWR of 1.25:1
- · Gold over Nickel Plated Beryllium Copper Contact
- 50 µin minimum contact plating

Applications:

- General Purpose Test
- Custom Cable Assemblies

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com





2.92mm Male Connector Clamp/Non-Solder Contact Attachment For .047 SR Cable from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: 2.92mm Male Connector Clamp/Non-Solder Contact Attachment For .047 SR Cable SMC292-0471

URL: https://www.fairviewmicrowave.com/2.92mm-male-standard-.047-sr-connector-smc292-0471-p.aspx









STANDARD TOLERANCES

.X ±0.2 .XX ±0.1 .XXX ±0.05

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
2.92mm Male Connector Clamp/Non-Solder Contact Attachment For .047 SR Cable	DWG NO SMC292-0471			CAGE CODE 3FKR5		
	CAD FILE 121516	SHEET	SCALE	N/A	SIZE A	41742