

## SMC292-0853 DATA SHEET

# 2.92mm Male Connector Solder Attachment for RG405, RG405 Tinned, .086 SR Cable

2.92mm male connector with solder attachment for RG405, RG405 Tinned and .086 SR, part number SMC292-0853, from Fairview Microwave is in-stock and ships same day. This 2.92mm male connector operates up to a maximum frequency of 40 GHz and offers excellent VSWR of 1.25:1.

Fairview's 2.92mm male connector SMC292-0853 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

#### **Electrical Specifications**

Description	Min	Тур	Max	Units
Frequency Range	DC		40	GHz
VSWR			1.25:1	

#### **Mechanical Specifications**

Size Length Width/Dia.

0.33 in [8.38 mm] 0.312 in [7.92 mm]

Weight

0.0105 lbs [4.76 g]

Mating Cycles

500 Cycles

#### **Material Specifications**

Description	Material	Plating	
Contact	Beryllium Copper	Gold over Nickel 50 µin minimum	
Body	Beryllium Copper	Gold over Nickel 50 µin minimum	
Coupling Nut	Passivated Stainless Steel	SAE-AMS-2700	

## **Environmental Specifications**

Temperature

Operating Range -55 to +100 deg C

**Compliance Certifications** (see product page for current document)

#### **Plotted and Other Data**

Notes:



### **Configuration:**

- 2.92mm Male Connector
- 50 Ohms
- Straight Body Geometry
- RG405, RG405 Tinned, .086 SR Interface Type
- Solder Attachment
- 5/16 inch Hex

#### **Features:**

- Operating Frequency of 40 GHz Max.
- Excellent VSWR of 1.25:1
- Gold over Nickel Plated Beryllium Copper Contact
- 50 µin minimum contact plating

## **Applications:**

- General Purpose Test
- Custom Cable Assemblies


Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com





#### **Assembly Instruction**



2.92mm Male Connector Solder Attachment for RG405, RG405 Tinned, .086 SR Cable from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 2.92mm Male Connector Solder Attachment for RG405, RG405 Tinned, .086 SR Cable SMC292-0853

URL: https://www.fairviewmicrowave.com/2.92mm-male-rg405-connector-smc292-0853-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





