

# SM5818 DATA SHEET

## N Male to RP N Female Adapter

## **Electrical Specifications**

Frequency Range Maximum VSWR DC to 11 GHz 1.3:1

## **Mechanical Specifications**

## Size

Length Width 1.73 in [43.94 mm] 0.83 in [21.08 mm]

#### Connector 1

Type

Inner Conductor Material and Plating Coupling Nut Material and Plating Body Material and Plating Dielectric Type N Male

Brass, Gold Brass, Nickel Brass, Nickel

PTFE



Type Inner Conductor Material and Plating Body Material and Plating Dielectric Type N Female Reverse Polarity Brass, Gold Brass, Nickel

PTFE

## **Environmental Specifications**

Compliance Certifications (visit www.FairviewMicrowave.com for current

document)

RoHS Compliant REACH Compliant


Yes 06/16/2014

### **Plotted and Other Data**

Notes:

· Values at 25 °C, sea level

## **Typical Performance Data**



E Dryle w Microwave

## Features:

- Connector 1: N MaleImpedance 1: 50 Ohms
- Connector 2: N Female Reverse Polarity
- Impedance 2: 50 OhmsAdapter Design: Standard
- Body Style: Straight

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





N Male to RP N Female Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order

For additional information on this product, please click the following link: N Male to RP N Female Adapter SM5818

URL: http://www.fairviewmicrowave.com/n-male-rp-n-female-adapter-sm5818-p.aspx

stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.	to implem	ient improv	vements.	. Fairview	/ Microw	ave reserv	es the righ	nt to mak	e such	changes	as requi	ired. Unles	s oth	erwise
	stated, al	l specificat	ions are	nominal.	Fairvie	w Microwa	ve does n	ot make	any rep	resentat	ion or w	varranty re	gardi	ng the
arising out of the use of any part or documentation.	suitability	of the par	t describ	ed hereir	n for any	/ particular	r purpose,	and Fair	view M	icrowave	does no	ot assume	any I	iability
	arising ou	t of the us	e of any	part or do	ocument	ation.								





FAIRVIEW MICROWAVE INC.  ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES:  1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  3. DIMENSIONS ARE IN INCHES [mm].							
N Male to RP N Female Adapter	DWG NO SM5818			CAGE CODE 3FKR5				
	CAD FILE 100114	SHEET	SCAL	E N/A	SIZE A	2233		