

SM9221 DATA SHEET

Ruggedized 2.4mm NMD Female to 2.4mm Female Adapter

Electrical Specifications

Frequency Range Maximum VSWR DC to 50 GHz 1.35:1

ave ave

• Connector 1: 2.4mm NMD Female

Mechanical Specifications

Size

Length Width 1.5 in [38.1 mm] 0.74 in [18.8 mm]

Connector 1

Type

Inner Conductor Material and Plating Inner Conductor Plating Specification Outer Conductor Material and Plating Coupling Nut Material and Plating Body Material and Plating Dielectric Type 2.4mm NMD Female Beryllium Copper, Gold 20µ" Minimum Passivated Stainless Steel Passivated Stainless Steel Passivated Stainless Steel

PSII

Adapter Design: RuggedizedBody Style: Straight

Impedance 1: 50 OhmsConnector 2: 2.4mm Female

• Impedance 2: 50 Ohms

Features:

Connector 2

Type

Inner Conductor Material and Plating Inner Conductor Plating Specification Outer Conductor Material and Plating Body Material and Plating Dielectric Type 2.4mm Female Beryllium Copper, Gold 20µ" Minimum Passivated Stainless Steel Passivated Stainless Steel PSU

Environmental Specifications Temperature

Operating Range

-55 to +100 deg C

Compliance Certifications (visit www.FairviewMicrowave.com for current document)

RoHS Compliant


Yes

Plotted and Other Data

Notes:

Values at 25 °C, sea level

Typical Performance Data



Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Ruggedized 2.4mm NMD Female to 2.4mm Female Adapter from Fairview Microwave is in-stock and available to ship sameday. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: Ruggedized 2.4mm NMD Female to 2.4mm Female Adapter SM9221

URL: http://www.fairviewmicrowave.com/ruggedized-2.4mm-nmd-female-2.4mm-female-adapter-sm9221-p.aspx









FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
Ruggedized 2.4mm NMD Female to 2.4mm Female Adapter	DWG NO SM9221			CAGE CODE 3FKR5		
	CAD FILE 021114	SHEET	SCALE	≣ N/A	SIZE A	2233