

RF Load 25 Watts Medium Power To 26.5 GHz Black Anodized Aluminum Heatsink 3.5mm Male

RF termination (also called RF load or dummy load) ST2635-25W from Fairview Microwave operates from DC to 26.5 GHz and handles up to 25 Watts (CW). This 3.5mm termination (or load) has a male gender. ST2635-25W 3.5mm load termination offers 1.3:1 max VSWR. This 25W 3.5mm terminator from Fairview Microwave has a heatsink body which is designed to provide adequate heat dissipation within its full frequency of operation.

RF terminations / loads are critical passive components in many RF, microwave and millimeter wave systems where signal reflection from unused ports can reduce the signal integrity can potentially damage the device. By terminating an unused port with a matched load (dummy load), the incident energy will be absorbed with minimal reflection. These radio frequency termination components are commonly used to terminate devices such as couplers, circulators, and switches. Loads / terminations are also widely used in measurement systems to ensure accurate results. Fairview offers a large selection of in-stock RF, microwave and millimeter wave terminations up to 65 GHz with great performance over the entire operating range and with power handling capabilities up to 800 Watts (CW).

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		26.5	GHz
Impedance		50		Ohms
VSWR			1.3:1	
Input Power (CW) derated linearly to 2.5W at +125°C			25	Watts
Input Power (Peak) 5µs pulse, 2.5% duty cycle			500	Watts

Mechanical Specifications

Size	
Length	1.59 in [40.39 mm]
Width	2 in [50.8 mm]
Weight	0.14639 lbs [66.4 g]

Configuration

Connector	3.5mm Male
-----------	------------

Material Specifications

Description	Material	Plating
Connector 1 Contact	Beryllium Copper	Gold MIL-G-45204
Body	Passivated Stainless Steel	
Housing	Black Anodized Aluminum Heatsink	



Features:

- DC to 26.5 GHz Frequency Range
- VSWR 1.3:1 Max
- Max Power 25 Watts (CW)
- 3.5mm Male Coaxial Interface

Applications:

- Wireless
- SatCom
- Radar Systems
- Test and Measurement
- Commercial and Military Communication

Fairview Microwave
 1130 Junction Dr. #100
 Allen, TX 75013
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Environmental Specifications

Temperature

Operating Range -55 to +125 deg C


Compliance Certifications (visit www.FairviewMicrowave.com for current document)

RoHS Compliant Yes
 REACH Compliant 12/17/2015

Plotted and Other Data

Notes:

Typical Performance Data




RF Load 25 Watts Medium Power To 26.5 GHz Black Anodized Aluminum Heatsink 3.5mm Male from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [RF Load 25 Watts Medium Power To 26.5 GHz Black Anodized Aluminum Heatsink 3.5mm Male ST2635-25W](http://www.fairviewmicrowave.com/rf-load-25-watts-26.5-ghz-precision-3.5mm-male-st2635-25w-p.aspx)

URL: <https://www.fairviewmicrowave.com/rf-load-25-watts-26.5-ghz-precision-3.5mm-male-st2635-25w-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



STANDARD TOLERANCES	
.X	±0.2
.XX	±0.1
.XXX	±0.05

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE RF Load 25 Watts Medium Power To 26.5 GHz Black Anodized Aluminum Heatsink 3.5mm Male		DWG NO ST2635-25W		CAGE CODE 3FKR5	
CAD FILE	041316	SHEET	SCALE	N/A	SIZE A 3045