

SMW22AC001-24F DATA SHEET

WR-22 to 2.4mm Female Waveguide to Coax Adapter UG-383/U Round Cover Flange With 33 GHz to 50 GHz Frequency Range For Q Band

The SMW22AC001-24F is a waveguide to coaxial adapter with a frequency range of 33 to 50 GHz, operating in the Q Band. This adapter offers a precision tolerance UG-383/U flange and a WR-22 waveguide interface size. The SMW22AC001-24F is constructed of gold plated aluminum to ensure durability and repeatable RF performance.

Configuration

Waveguide Size WR-22

Flange UG-383/U Round Cover

RF Connector
Impedance
Body Geometry

2.4mm Female
50 Ohms
Right Angle

Electrical Specifications

Description	Min	Тур	Max	Units	
Frequency Range	33		50	GHz	
VSWR			1.33:1		
Insertion Loss			0.4	dB	

Mechanical Specifications

Size

 Length
 1 in [25.4 mm]

 Width
 1.13 in [28.7 mm]

 Height
 1.13 in [28.7 mm]

 Weight
 0.0305 lbs [13.83 g]

RF Connector

Connector Type 2.4mm Female Body Material and Plating Stainless Steel

Waveguide Interface

Waveguide Type

Flange Type

Flange Designation

Body Material and Plating

Plating Specification

WR-22

Round Cover

UG-383/U

Aluminum, Gold

ASTMB488

Environmental Specifications

Temperature

Operating Range -40 to +85 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Values at +25 °C, sea level unless stated otherwise



Features:

- Q Band, 33 to 50 GHz Frequency Range
- WR-22 Waveguide Interface with Precision Tolerance UG-383/U Flange
- 2.4 mm Female RF Interface
- Comprehensive waveguide offering also includes E-Bends, H-Bends, Sections, Filters, Terminations, Couplers, and more.


Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013


Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com



Typical Performance Data









WR-22 to 2.4mm Female Waveguide to Coax Adapter UG-383/U Round Cover Flange With 33 GHz to 50 GHz Frequency Range For Q Band from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: WR-22 to 2.4mm Female Waveguide to Coax Adapter UG-383/U Round Cover Flange With 33 GHz to 50 GHz Frequency Range For Q Band SMW22AC001-24F

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order

URL: https://www.fairviewmicrowave.com/wr-22-2.4mm-waveguide-coax-adapter-50-ghz-smw22ac001-24f-p.aspx

to implem	ent improve	ements.	Fairview	Microw	ave reserv	es the rigl	nt to ma	ke sucl	n changes	as req	uired	. Unles	ss ot	herwise
stated, al	specification	ons are i	nominal.	Fairvie	w Microwa	ve does n	ot make	any r	epresentat	ion or	warr	anty re	gard	ling the
suitability	of the part	describe	ed hereir	for any	/ particular	purpose,	and Fai	rview	Microwave	does	not a	ssume	any	liability
arising ou	t of the use	of any p	art or do	ocument	ation.									





FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].						
WR-22 to 2.4mm Female Waveguide to Coax Adapter UG-383/U Round Cover Flange With 33 GHz to 50 GHz Frequency Range For Q Band	DWG NO SMW22AC001-24F				CAGE CODE 3FKR5		
	CAD FILE	101915	SHEET	SCALI	E N/A	SIZE A	150

- LABEL