



# Push-On RA SMP Female to RA Push-On SMP Female Cable RG-316 Coax

The RA SMP female push-on to RA SMP female push-on cable using RG-316 coax, part number FMC00350, from Fairview Microwave is in-stock and ships same day. This Fairview SMP to SMP cable assembly has a female to female gender configuration with 50 ohm flexible RG316 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC00350 SMP female to SMP female cable assembly operates to 3 GHz. The right angle SMP interfaces on the RG316 cable allow for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

## **Electrical Specifications**

Description	Min	Т	ур	Max	Units
Frequency Range	DC			3	GHz
VSWR				1.4:1	
Velocity of Propagation			69		%
Capacitance		29.4	[96.46	]	pF/ft [pF/m]
Operating Voltage (AC)				350	Vrms
Jacket Spark				2,000	Vrms

## **Performance by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	3	GHz
Insertion Loss (Max.)	0.11	0.13	0.17	0.38	0.58	dB/ft
	0.36	0.43	0.56	1.25	1.9	dB/m

#### **Electrical Specification Notes:**

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.2 dB per connector.

#### **Mechanical Specifications**

## **Cable Assembly**

Diameter 0.157 in [3.99 mm]

#### Cable

Cable Type
Impedance
Inner Conductor Type
Inner Conductor Material and Plating
Dielectric Type
Number of Shields
Shield Layer 1
Jacket Material

RG316

50 Ohms Stranded Copper Clad Steel, Silver

PTFE 1

Silver Plated Copper Braid FEP, Tan

REV 1.0 Page



# **Configuration:**

- Push-OnSMP Female Right Angle
- Push-OnSMP Female Right Angle
- RG316

### Features:

- Max Frequency 3 GHz
- 69% Phase Velocity
- FEP Jacket

# **Applications:**

- General Purpose
- Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Jacket Diameter

0.102 in [2.59 mm]

#### **Connectors**

Description	Connector 1	Connector 2		
Туре	SMP Female	SMP Female		
Specification	MIL-STD-348A	MIL-STD-348A		
Impedance	50 Ohms	50 Ohms		
Connection Method	Push-On	Push-On		
Contact Material & Plating	Beryllium Copper, Gold	Beryllium Copper, Gold		
Contact Plating Spec.	30µ in. minimum	30μ in. minimum		
Dielectric Type	PTFE	PTFE		
Outer Cond Material & Plating	Beryllium Copper, Gold	Beryllium Copper, Gold		
Outer Cond Plating Spec.	3µ in. minimum	3µ in. minimum		
Body Material & Plating	Brass, Gold	Brass, Gold		
Body Plating Spec.	3μ in. minimum	3µ in. minimum		

# **Environmental Specifications**

Temperature

Operating Range

-55 to +165 deg C

**Compliance Certifications** (see product page for current document)

# **Plotted and Other Data**

Notes:

• Values at 25°C, sea level.

#### **How to Order**

Part Number Configuration:

FMC00350 - xx uu | cm = Centimeters | chlank > = Inches | Length

Example: FMC00350-12 = 12 inches long cable

FMC00350-100cm = 100 cm long cable

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2020

REV 1.0 Page 2 of 4





Push-On RA SMP Female to RA Push-On SMP Female Cable RG-316 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: Push-On RA SMP Female to RA Push-On SMP Female Cable RG-316 Coax FMC00350

URL: https://www.fairviewmicrowave.com/ra-smp-female-ra-smp-female-cable-rg316-coax-fmc00350-p.aspx







