

SMW75TF005-24 DATA SHEET

WR-75 Twistable Flexible Waveguide Using Square Cover Flange With a 10 GHz to 15 GHz Frequency Range

The SMW75TF005-24 is one of Fairview Microwave's flexible, twistable sections which operates in the 10 to 15 GHz range. It can be twisted and/or bent in both the E and H planes without impairing VSWR or attenuation because of its silver coated helically wound brass body construction. The twistable section is covered in a neoprene jacket which allows the section to be pressurized as well as protecting the waveguide's integrity.

Electrical Specifications

| Min | Тур | Max | Units |
|-----|-------|-----|----------------|
| 10 | | 15 | GHz |
| | 1.1:1 | | |
| | 0.36 | | dB |
| | | 10 | 10 15 1.1:1 |

Mechanical Specifications

| chamical Specification | 113 |
|-------------------------|------------------|
| Waveguide Size | |
| Waveguide Design | |
| Section Length | |
| E-Plane Minimum Bend Ra | adius, One Time |
| E-Plane Minimum Bend Ra | adius, Repeated |
| H-Plane Minimum Bend R | Radius, One Time |
| H-Plane Minimum Bend R | Radius, Repeated |
| Maximum Offset Rotation | ı, One Time |
| Maximum Offset Rotation | i, Repeated |
| Maximum Operating Press | sure |

WR-75
Twistable
24 in [609.6 mm]
2.5 in [63.5 mm]
10 in [254 mm]
4.5 in [114.3 mm]
20 in [508 mm]
112 degrees/ft
28 degrees/ft
45 psig

| Description | Flange 1 | Waveguide | Flange 2 |
|-------------|--------------|-----------|--------------|
| Туре | Square Cover | WR-75 | Square Cover |
| Designation | None | | None |
| Material | Brass | Brass | Brass |
| Plating | | Silver | |
| Color | Gold | Black | Gold |

Compliance Certifications (visit www.FairviewMicrowave.com for current document)

RoHS Compliant Yes

REACH Compliant 12/17/2015

Plotted and Other Data

Notes:

· Notes, Plotted Data



Features:

- Twistable/Flexible in both the E and H plane
- Neoprene Jacket allows pressurization
- 10 GHz to 15 GHz Range
- Brass flanges with a silver plated brass body

Applications:

- Test Benches
- · Microwave Radio
- Pressurized waveguide systems
- · Provides vibration isolation
- Easily connects misaligned sections.
- Relieves mechanical stresses caused by thermal expansion/contraction.


Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com



Typical Performance Data




WR-75 Twistable Flexible Waveguide Using Square Cover Flange With a 10 GHz to 15 GHz Frequency Range from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: WR-75 Twistable Flexible Waveguide Using Square Cover Flange With a 10 GHz to 15 GHz Frequency Range SMW75TF005-24

URL: https://www.fairviewmicrowave.com/wr-75-twistable-flexible-waveguide-square-10-15-ghz-smw75tf005-24-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





| FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM | NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm]. | | | | |
|--|---|-------|-------|-----------------|--------|
| WR-75 Twistable Flexible Waveguide Using Square Cover Flange With a 10 GHz to 15 GHz Frequency Range | SMW75TF005-24 | | | CAGE CODE 3FKR5 | |
| | CAD FILE 100515 | SHEET | SCALE | ≣ N/A | SIZE A |