

**Type N Fixed Torque Wrench in Click Type 20mm Bit that is Pre-set to 8.85 in-lbs**



**Configuration**

Torque Type	Fixed
Design Type	Click
Hex Size	20 mm
Torque Setting	8.85 in-lbs [1 Nm]
Torque Accuracy	±0.354 in-lbs [±0.04 Nm]
Torque Accuracy Percentage	±4 %

**Size**

Length	7.45 in [189.23 mm]
Handle Diameter	0.688 in [17.48 mm]
Weight	0.392 lbs [177.81 g]

**Compliance Certifications** (see [product page](#) for current document)

**Notes:**

- Do not use on damaged connectors.
- To improve performance of a wrench that hasn't been used recently, actuate the wrench by clicking the wrench head back and forth several times before use. This will spread the lubricant through the internal mechanism.
- Click type tools require smooth consistent application of force. Each torquing action should be completed within 2 seconds. Slower or faster torquing action will detract from accuracy.

Type N Fixed Torque Wrench in Click Type 20mm Bit that is Pre-set to 8.85 in-lbs from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Type N Fixed Torque Wrench in Click Type 20mm Bit that is Pre-set to 8.85 in-lbs ST-N5](#)

URL: <https://www.fairviewmicrowave.com/n-fixed-torque-wrench-click-st-n5-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.


**Features:**

- Designed for continual use
- Torque wrench will "click" once torque value force is achieved
- Designed to prevent over torque
- 

**Applications:**

- Attaching Test Cables in Lab Environments
- Final production attachment of product
- Field install and testing applications
- Anytime accurate torque is needed while preventing over-torque

Fairview Microwave  
 301 Leora Ln., Suite 100  
 Lewisville, TX 75056  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)



<b>FAIRVIEW MICROWAVE INC.</b> ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE Type N Fixed Torque Wrench in Click Type 20mm Bit that is Pre-set to 8.85 in-lbs		DWG NO <b>ST-N5</b>		CAGE CODE <b>3FKR5</b>	
CAD FILE	051815	SHEET	SCALE	N/A	SIZE A 5568