



# 4.3-10 M/F In/Out Bulkhead Coaxial RF Surge Protector, 698MHz - 2.7GHz, DC Block, 500W, IP67, 40kA, Filter, Low PIM -173 dBc

RF surge protector (also known as lightning arrester) FMSP1060 from Fairview Microwave utilizing a patented spiral inductor design enables an almost instantaneous response to a lightning surge to protect critical hardware while maintaining the RF performance. This RF surge protector component is manufactured in a coaxial in-line design with wide operating frequency range. All Fairview Microwave RF surge protector products are available in stock with same day shipping.

Surge Protector Type DC Handling	Surge Filter DC Block				
Description	Min	Тур	)	Max	Unit
Frequency Range	0.698			2.7	GHz
Impedance		50			Ohm
VSWR				1.1:1	
Return Loss				26	dB
Insertion Loss				0.1	dB
Passive Intermodulation				-173	dBc
Input Power, CW 500W @ 920MHz 750W @ 50°C				500	Watt
Surge Current				40	kA
IEC 61000-4-5 8/20μs	WAVEFORM				
Throughput Energy FOR 3kA@ 8/20µs WA	VEFORM			0.5	nJ



### Features:

- · Surge current of 40kA
- Max Power 500W
- Frequency range from 698 MHz to 2.7 GHz
- Waterproof IP67 rated
- 4.3-10 male connector to 4.3-10 female connector
- DC Block
- Low PIM
- VSWR < 1.1:1
- Low insertion loss
- · CE & RoHS compliant

## Applications:

- Cellular communication systems
- Public safety systems
- Emergency response systems
- Industrial

### **Mechanical Specifications**

Configuration

Input Connector 4.3-10 Male Output Connector 4.3-10 Female

**Environmental Specifications** 

**Temperature** 

Operating Range -50 to 85 deg C

Ingress Protection (IP) Rating IP 67

**Compliance Certifications** (see product page for current document)

#### **Plotted and Other Data**

Notes:

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





4.3-10 M/F In/Out Bulkhead Coaxial RF Surge Protector, 698MHz - 2.7GHz, DC Block, 500W, IP67, 40kA, Filter, Low PIM -173 dBc from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: 4.3-10 M/F In/Out Bulkhead Coaxial RF Surge Protector, 698MHz - 2.7GHz, DC Block, 500W, IP67, 40kA, Filter, Low PIM -173 dBc FMSP1060

URL: https://www.fairviewmicrowave.com/4.3-10-surge-protector-2.7ghz-filter-fmsp1060-p.aspx









STANDARD TOLERANCES

.X ±0.2 .XX ±0.01 .XXX ±0.005

\*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

Fairview Microwave	NOTES:  1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  3. DIMENSIONS ARE IN INCHES [mm].							
4.3-10 M/F In/Out Bulkhead Coaxial RF Surge Protector, 698MHz - 2.7GHz, DC Block, 500W, IP67, 40kA, Filter, Low PIM -173 dBc	DWG NO FMSF		CAGE CODE 3FKR5					
	CAD FILE 3/2/18	SHEET 1 OF 1	SCALI	E N/A	SIZE A	xxxx		