

FMWAN159-10NF DATA SHEET

WR-159 Standard Gain Horn with 10 dBi gain, N Female connector

The FMWAN159-10NF standard gain horn antenna (also known as waveguide horn) from Fairview Microwave is part of our comprehensive selection of waveguide antennas. This standard gain horn is mated with a WR-159 to N Female waveguide to coaxial adapter and operates from 4.9 GHz to 7.05 GHz.

Our FMWAN159-10NF standard gain horn antenna has a nominal gain of 10 dBi with a Horizontal and Vertical HPBW (Half Power Beam Width) of 52.1 dB and 51.6 dB respectively. Fairview Microwave's N Female to WR-159 standard gain horns are available in 10, 15 and 20 dBi models with pyramidal shape and connectorized input.

Waveguide antennas, such as the FMWAN159-10NF are used in a wide variety of applications due to the high-power handling capability, low loss, high directivity, and near constant electrical performance. Our WR-159 waveguide antennas with N Female interface is part of over 40,000 RF, microwave and millimeter wave components from Fairview Microwave available worldwide and Ship same day.

ns				
Min	Ту	p	Max	Units
4.9			7.05	GHz
Gain Horn				
	1(C		dBi
Width	52	.1		Degrees
dth	51	.6		Degrees
Adapter				
			1.3:1	
ions	2.417 in 1.94 in 4	61.39 r 19.28 m	nm m	
	0.5875 l	DS 200.4	+9 Y	
e	0.58751 N Femal		+9 Y	
	4.9 Gain Horn Width dth I Adapter	Gain Horn 10 Width 52 dth 51 I Adapter 10 ions 5.65 in 1 2.417 in 10	Gain Horn 10 Width 52.1 dth 51.6 I Adapter	Gain Horn 10 Width 52.1 dth 51.6 I Adapter 1.3:1

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:



Features:

- 4.9 GHz to 7.05 GHz
- WR-159 Waveguide Band
- 10 dBi Nominal Gain
- N Female Connector

Applications:


- Antenna Measurements
- Wireless Communication
- Laboratory Use
- Microwave Radio Systems
- Radome Testing
- Automotive Antenna Test Solutions
- Radar Cross Section
- Satellite Antenna Testing

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com






Typical Performance Data



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689






WR-159 Standard Gain Horn with 10 dBi gain, N Female connector from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: WR-159 Standard Gain Horn with 10 dBi gain, N Female connector FMWAN159-10NF

URL:



Fairview Microwave



an INFINIT[®] brand

