

## FMC0919315LF DATA SHEET

# MMCX Plug to RA MMCX Plug Cable RG-316 Coax with LF Solder

The MMCX plug to RA MMCX plug cable using RG-316 coax, part number FMC0919315LF, from Fairview Microwave is in-stock and ships same day. This Fairview MMCX to MMCX cable assembly has a plug to plug gender configuration with 50 ohm flexible RG-316 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC0919315LF MMCX plug to MMCX plug cable assembly operates to 3 GHz. The right angle MMCX interface on the RG-316 cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

### **Electrical Specifications**

Description	Min	Т	ур	Max	ι	Jnits
Frequency Range	DC			3		GHz
VSWR				1.35:1		
Velocity of Propagation		7	70			%
Capacitance		32 [1	04.99	9]	pF/f	t [pF/m]

### **Mechanical Specifications**

Cable Assembly Length*	0 in [0 mm]
Cable Cable Type Impedance Inner Conductor Type Inner Conductor Material and Dielectric Type Number of Shields Shield Layer 1 Jacket Material Jacket Diameter	Plating Plating RG-316 50 Ohms Stranded Copper, Silver PTFE 1 Silver Plated Copper Braid FEP, Tan 0.098 in [2.49 mm]



## **Configuration:**

- MMCX Plug
- MMCX Plug Right Angle
- RG-316

## **Features:**

- Max Frequency 3 GHz
- 70% Phase Velocity
- FEP Jacket

## **Applications:**

- General Purpose
- Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com Fairview Microwave

an INFINIT<sup>©</sup> brand



#### Connectors

Description	Connector 1	Connector 2	
Туре	MMCX Plug	MMCX Plug	
Configuration	Straight	Right Angle	
Impedance	50 Ohms	50 Ohms	
Contact Material & Plating	Brass, Gold	Brass, Gold	
Contact Plating Spec.	30µ in. minimum		
Dielectric Type	PTFE	PTFE	
Body Material & Plating	Brass, Gold	Brass, Gold	
Body Plating Spec.	3µ in. minimum		
nvironmental Specificat Temperature Operating Range ompliance Certification lotted and Other Data Notes:	-55 to +:	155 deg C rrent document)	
ow to Order			
Part Number Configuration	FMC091	9315LF - xx	uu   cm = Centimeters <blank> = Inches</blank>
	F-12 = 12 inches long cab F-100cm = 100 cm long ca		Length

MMCX Plug to RA MMCX Plug Cable RG-316 Coax with LF Solder from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: MMCX Plug to RA MMCX Plug Cable RG-316 Coax with LF Solder FMC0919315LF


URL: https://www.fairviewmicrowave.com/standard-mmcx-plug-ra-mmcx-plug-cable-rg316-coax-fmc0919315lf-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].						
TITLE MMCX Plug to RA MMCX Plug Cable RG-316 Coax with	DWG NO FMC0919315LF				CAGE CODE 3FKR5		
LF Solder	CAD FILE 102814	SHEET	SCAL	E N/A	SIZE A	5568	

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689