

SMA Female to SSMC Plug Cable RG-316 Coax with LF Solder

The SMA female to SSMC plug cable using RG-316 coax, part number FMC1334315LF, from Fairview Microwave is in-stock and ships same day. This Fairview SMA to SSMC cable assembly has a female to plug gender configuration with 50 ohm flexible RG-316 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC1334315LF SMA female to SSMC plug cable assembly operates to 3 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Тур		Max	Units	
Frequency Range	DC			3		GHz
VSWR				1.35:1		
Velocity of Propagation		7	70			%
Capacitance		32 [104.99]		pF/ft [pF/m]		

Mechanical Specifications

Cable Assembly Length*

Cable

Cable Type Impedance Inner Conductor Type Inner Conductor Material and Plating Dielectric Type Number of Shields Shield Layer 1 Jacket Material Jacket Diameter 0 in [0 mm]

RG-316 50 Ohms Solid Copper, Silver PTFE 1 Silver Plated Copper Braid FEP, Tan 0.098 in [2.49 mm]



FMC1334315LF



Configuration:

- SMA Female
- SSMC Plug
- RG-316

Features:

- Max Frequency 3 GHz
- 70% Phase Velocity
- FEP Jacket

Applications:

- General Purpose
- Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com Fairview Microwave

an INFINIT[©] brand



Connectors

Description	Connector 1	Connector 2	—
Туре	SMA Female	SSMC Plug	-
Impedance	50 Ohms	50 Ohms	—
Mating Cycles		500	
Contact Material & Plating	Beryllium Copper, Gold	Beryllium Copper, Gold	
Contact Plating Spec.	50µ in. minimum	MIL-G-45204	
Dielectric Type	PTFE	PTFE	—
Body Material & Plating	Brass, Gold	Beryllium Copper, Gold	_
Body Plating Spec.	3µ in. minimum		
Coupling Nut Material & Plating		Brass, Gold	
Hex Size	1/4 inch	5/32 inch	
Operating Range Compliance Certifications Plotted and Other Data Notes:		+165 deg C current document)	
low to Order			
Part Number Configuration:	FMC13	34315LF - xx	uu cm = Centimeters <blank> = Inches Length</blank>
	12 = 12 inches long ca 100cm = 100 cm long		

SMA Female to SSMC Plug Cable RG-316 Coax with LF Solder from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: SMA Female to SSMC Plug Cable RG-316 Coax with LF Solder FMC1334315LF


URL: https://www.fairviewmicrowave.com/sma-female-ssmc-plug-cable-rg316-coax-fmc1334315lf-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					NY TIME.
	DWG NO FMC1334315LF			CAGE CODE 3FKR5		
SMA Female to SSMC Plug Cable RG-316 Coax with LF						
Solder	CAD FILE 101414	SHEET	SCALE	N/A	SIZE A	5568

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689