

FMCA2699 DATA SHEET

BNC Male Right Angle to TNC Female Cable Using RG223 Coax

The RA BNC male to TNC female cable using RG223 coax, part number FMCA2699, from Fairview Microwave is in-stock and ships same day. This Fairview BNC to TNC cable assembly has a male to female gender configuration with 50 ohm flexible RG223 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The right angle BNC interface on the RG223 cable allows for easier connections in tight spaces. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

	Min	Тур	Max	Units
Velocity of Propagation		66		%
Capacitance		30.8 [<mark>101.(</mark>)5]	pF/ft [pF/m]
hanical Specificati	ons			
Cable Assembly				
Weight		0.08 lbs [36.29 g]		
Cable Cable Type Impedance Inner Conductor Type Inner Conductor Materia Dielectric Type Number of Shields Shield Layer 1	al and Plating	RG223 50 Ohms Solid Copper, Silver PE 2 Silver Plated Copper Braid Silver Plated Copper Braid PVC, Black 0.209 in [5.31 mm]		
Shield Layer 2 Jacket Material Jacket Diameter				
Repeated Minimum Bend Radius		1 in [25.4 mm]		



Configuration:

- BNC Male Right Angle
- TNC Female
- RG223

Features:

- 66% Phase Velocity
- Double Shielded
- PVC Jacket

Applications:


- General Purpose
- Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com Fairview Microwave

an INFINIT brand



Connectors



BNC Male Right Angle to TNC Female Cable Using RG223 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: BNC Male Right Angle to TNC Female Cable Using RG223 Coax FMCA2699


URL: https://www.fairviewmicrowave.com/ra-bnc-male-to-tnc-female-cable-rg223-coax-fmca2699-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689