

RG55-BULK DATA SHEET

RG55 53 Ohm Flexible Coax Cable Black PE Jacket

RG55 coax cable from Fairview is only one of a large number of radio frequency twinaxial and coaxial cable types specifically stocked to be ready for quick shipment. Fairview Microwave RG55 coax cable is manufactured in a flexible design and has a 53 ohm impedance. This flexible 53 Ohm coax cable RG55 is constructed with a 0.163 inch diameter and PE jacket.

RG55 53 Ohm coax cable with PE jacket is rated for a 3,000 MHz maximum operating frequency. This 53 Ohm 0.163 inch diameter and flexible coax cable is built with shield count of 2. Fairview Microwave RG55 coax is constructed with PE dielectric and a maximum operating temperature of 80 degrees C.



Configuration:

- Flexible Cable
- 2 Shield(s)

Electrical Specifications

Description	Min	т	ур	Max	Un	its
Frequency Range	DC			3	G	Hz
Impedance		53 ±2		Ohms		
Velocity of Propagation		66		%		
Nominal Capacitance		28.8		pF	pF/ft	
		[94.49]		[pF/m]		

Performance by Frequency Band

Description	F1	F2	F3	F4	F5	Units
Frequency	0.01	0.1	1	3		GHz
Attenuation, Typ	1.35 4.43	4.3 14.11	16.5 54.13	32 104.99		dB/100ft dB/100m

Mechanical Specifications

Diameter Weight 0.202 in [5.13 mm] 0.03 lbs/ft [0.04 kg/m]

Construction Specifications

Description	Material and Plating	Diameter
Inner Conductor	Copper, Silver, 1 Strands	0.032 in [0.81 mm]
Conductor Type	Solid	
Dielectric	PE	0.116 in [2.95 mm]
First Shield	Tinned Copper Braid	[]
Second Shield	Tinned Copper Braid	[]
Jacket	PE, Black	0.202 in [5.13 mm]

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Environmental Specifications

Temperature Operating Range

80 to -40 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data Notes:

RG55 53 Ohm Flexible Coax Cable Black PE Jacket from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: RG55 53 Ohm Flexible Coax Cable Black PE Jacket RG55-BULK


URL: https://www.fairviewmicrowave.com/rg55-flexible-coax-cable-pe-jacket-rg55-bulk-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

an INFINIT[®] brand





301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689