

## SSMA Female Connector Solder Attachment 4 Hole Flange for FM-SR086ALTN, FM-SR086TB, RG405, .232 inch Hole Spacing

SSMA female 4 hole flange mount connector with solder/solder attachment for FM-SR086ALTN, FM-SR086TB and RG405 (.232 inch hole spacing), part number FMCN1871, from Fairview Microwave is in-stock and ships same day. Fairview's FMCN1871 4 hole flange SSMA connector enables designers to make external connections on product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Fairview's SSMA female 4 hole flange connector FMCN1871 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

### Mechanical Specifications

<b>Size</b>	
Length	0.5 in [12.7 mm]
Width/Dia.	0.38 in [9.65 mm]
Height	0.38 in [9.65 mm]
Weight	0.005 lbs [2.27 g]

### Material Specifications

Description	Material	Plating
Contact		Gold MIL-G-45204
Insulation	Teflon	
Body	Stainless Steel	Gold MIL-G-45204

### Environmental Specifications

#### Temperature

Operating Range -65 to +165 deg C

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:



### Configuration:

- SSMA Female Connector
- MIL-C-39012
- 50 Ohms
- Straight Body Geometry
- FM-SR086ALTN, FM-SR086TB, RG405 Interface Type
- Solder/Solder Attachment
- 4 Hole Flange

### Features:

- Gold Plated Contact
- Contact plating according to MIL-G-45204

### Applications:

- General Purpose Test
- Rack and Panel Mount Applications
- Custom Cable Assemblies

Fairview Microwave  
301 Leora Ln., Suite 100  
Lewisville, TX 75056  
Tel: 1-800-715-4396 / (972) 649-6678  
Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)


SSMA Female Connector Solder Attachment 4 Hole Flange for FM-SR086ALTN, FM-SR086TB, RG405, .232 inch Hole Spacing from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [SSMA Female Connector Solder Attachment 4 Hole Flange for FM-SR086ALTN, FM-SR086TB, RG405, .232 inch Hole Spacing FMCN1871](#)

URL: <https://www.fairviewmicrowave.com/ssma-female-fm-sr086altn-fm-sr086tb-rg405-connector-fmcn1871-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





SSMA Female Connector Solder Attachment 4 Hole Flange for FM-SR086ALTN, FM-SR086TB, RG405, .232 inch Hole Spacing