



SMA Male to SMB Jack Adapter

SMA male to SMB jack adapter part number SM2063 from Fairview Microwave is in-stock and ships same day. This Fairview SMA to SMB adapter has a male to jack gender configuration. SM2063 SMA male to SMB jack adapter operates to 4 GHz. The Fairview Microwave RF adapter provides excellent VSWR of 1.2:1 maximum. The SMA connector mates mechanically with commercially available 3.5mm and 2.92mm (K) connectors.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Min Typ		Max	Units		
Frequency Range	DC		4	GHz		
VSWR			1.2:1			

Electrical Specification Notes: Values at 25°C, sea level.

Mechanical Specifications

Siz	ze
-----	----

Length	0.81 in [20.57 mm]
Weight	0.0075 lbs [3.4 g]

Description	Connector 1	Connector 2
Туре	SMA Male	SMB Jack
Polarity	Standard	Standard
Interface Specification	MIL-STD-348	MIL-STD-348



Configuration:

- SMA Male Connector 1
- SMB Jack Connector 2
- 50 Ohm
- Straight Body Geometry

Features:

- VSWR of 1.2:1 max up to 4 GHz
- SMA interface meets MIL-STD-348
- SMB interface meets MIL-STD-348
- Contact plating according to MIL-G-45204
- Gold Plated Contact

Applications:

- Enables Between Series Connections
- General Purpose Test

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com





Material Specifications

Description	Connector 1	Connector 2			
Туре	SMA Male	SMB Jack			
Contact Plating	Gold	Gold			
Contact Plating Spec.	MIL-G-45204	MIL-G-45204			
Insulation Material	PTFE	PTFE			
Outer Contact Material		Brass			
Outer Contact Plating	Nickel				
Outer Conductor Contact Spe	ec.	QQ-N-290			
Body Material	Brass				
Body Plating	Nickel				
Body Plating Spec.	QQ-N-290				
Coupling Nut Material	Brass				
Coupling Nut Plating	Nickel				
Coupling Nut Plating Spec.	QQ-N-290				

Environmental Specifications

TemperatureOperating Range


-65 to +165 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Typical Performance Data







SMA Male to SMB Jack Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF ondemand.

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order


For additional information on this product, please click the following link: SMA Male to SMB Jack Adapter SM2063

URL: https://www.fairviewmicrowave.com/sma-male-smb-jack-adapter-sm2063-p.aspx

stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.		ient improv												
	stated, al	l specificati	ons are	nominal.	Fairvie	w Microwa	ve does n	ot make	any rep	resentat	ion or v	warranty re	gard	ling the
arising out of the use of any part or documentation.	suitability	of the part	t describ	ed hereir	for any	/ particulai	r purpose,	and Fair	view Mi	crowave	does n	ot assume	any	liability
	arising ou	t of the use	of any	part or do	cument	ation.								







STANDARD TOLERANCES

.X ±0.2 .XX ±0.1 .XXX ±0.05

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].						
SMA Male to SMB Jack Adapter	DWG NO SM2063			CAGE CODE 3FKR5			
	CAD FILE 093016	SHEET	SCAL	E N/A	SIZE A	2233	