



WR-229 to Type N Female Waveguide to Coax Adapter CPR-229G Grooved with 3.3 GHz to 4.9 GHz U Band in Aluminum, Paint

The FMWCA1062 is a waveguide to coaxial adapter operating in the U Band with a 3.3 to 4.9 GHz frequency range. This adapter offers a WR-229 waveguide interface size using a standard CPR-229G Flange. The FMWCA1062 is constructed of Aluminum Alloy and painted to ensure durability. The coaxial connector offered by this adapter uses a N Female Connector.

Configuration

Waveguide Size WR-229
Flange CPR-229G
RF Connector N Female
Impedance 50 Ohms
Body Geometry Right Angle

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	3.3		4.9	GHz
VSWR		1.25:1		

Mechanical Specifications

RF Connector

Connector Type N Female

Waveguide Interface

Waveguide Type WR-229
Flange Type CPR-229G
Body Material and Plating Aluminum, Paint

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Values at +25 °C, sea level unless stated otherwise



Features:

- U Band
- 3.3 to 4.9 GHz Frequency Range
- WR-229 Waveguide Interface
- · CPR-229G Flange
- N Female RF Interface
- · Right Angle

Applications:


- Test Benches
- Radar
- Satellite
- · Microwave Radio Systems
- · Military and Space
- Communication Systems

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Typical Performance Data



WR-229 to Type N Female Waveguide to Coax Adapter CPR-229G Grooved with 3.3 GHz to 4.9 GHz U Band in Aluminum, Paint from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: WR-229 to Type N Female Waveguide to Coax Adapter CPR-229G Grooved with 3.3 GHz to 4.9 GHz U Band in Aluminum, Paint FMWCA1062

URL: https://www.fairviewmicrowave.com/wr229-type-n-female-waveguide-coax-adapter-cpr-229g-grooved-fmw-ca1062-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.







STANDARD TOLERANCES

.X ±0.2 .XX ±0.01 .XXX ±0.005

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

Fairview Microwave	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].						
TITLE	DWG NO FMWCA1062			CAGE CODE 3FKR5			
WR-229 to Type N Female Waveguide to Coax Adap CPR-229G Grooved with 3.3 GHz to 4.9 GHz U Band Aluminum, Paint	CAD FILE 10/04/18	SHEET 1 OF 1	SCAL	E N/A	SIZE A	7361	