



WR-284 to Type N Female Waveguide to Coax Adapter UDR32 with 2.6 GHz to 3.95 GHz in Aluminum

The FMWCA1081 is a right angle waveguide to coaxial adapter operating at a frequency range of 2.6 GHz to 3.95 GHz. This adapter offers a WR-284 waveguide interface size coupled with a precision tolerance UDR32 flange. The FMWCA1081 is constructed of aluminum and painted gray to ensure durability. The coaxial connector offered by this adapter uses an N Female connector.

Configuration

Waveguide Size WR-284
Flange UDR32
RF Connector N Female
Body Geometry Right Angle

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	2.6		3.95	GHz
VSWR			1.25:1	
Insertion Loss			0.2	dB
Input Power (CW)			100	Watts

Mechanical Specifications

Size

 Length
 2.83 in [71.88 mm]

 Width
 4.5 in [114.3 mm]

 Height
 3 in [76.2 mm]

RF Connector

Connector Type N Female

Waveguide Interface

Waveguide Type WR-284
Flange Type UDR32
Body Material and Plating Aluminum

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

• Values at +25 °C, sea level unless stated otherwise



Features:

- 2.6 GHz to 3.95 GHz
 Frequency Range
- WR-284 Waveguide Interface
- UDR32 Flange
- N Female RF Interface
- Comprenhensive waveguide offering also include E-Bends, H-Bends, Sections, Filters, Terminations, Couplers, and more.

Applications:

- Test Benches
- Radar
- Satellite
- · Microwave Radio Systems
- · Military and Space
- Communication Systems

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com

sales@fairviewmicrowave.com





WR-284 to Type N Female Waveguide to Coax Adapter UDR32 with 2.6 GHz to 3.95 GHz in Aluminum from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: WR-284 to Type N Female Waveguide to Coax Adapter UDR32 with 2.6 GHz to 3.95 GHz in Aluminum FMWCA1081

URL: https://www.fairviewmicrowave.com/wr284-type-n-female-waveguide-coax-adapter-udr32-fmwca1081-p.aspx







