


## 30 dB WR-159 Waveguide Crossguide Coupler with CPR-159F Flange and N Female Coupled Port from 4.64 GHz to 7.05 GHz in Aluminum

The FMWCP1082-30 is a 30 dB WR-159 three port crossguide coupler with integrated N Female connector for the coupled port. This coupler can be mounted directly into the waveguide signal path, connected via coax to allow signal sampling /monitoring. The coupler has a typical VSWR of 1.1:1 and are made of Aluminum with CPR-159F flanges. The FMWCP1082-30 is part of a family of cross guide couplers offered by Fairview Microwave with coupling values ranging from 20 to 50 dB.



### Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	4.64		7.05	GHz
<b>Coupler</b>				
Nominal Coupling Level		30		dB
Coupling Accuracy			±1.5	dB
Directivity	18			dB
Insertion Loss		0.1		dB
Main Line VSWR			1.1:1	
Secondary Line VSWR			1.25:1	
Input Power (CW)			1.2	kWatts
Input Power Peak			500	kWatts

### Mechanical Specifications

<b>Size</b>	
Length	6.693 in [170 mm]
Width	4.724 in [119.99 mm]
Height	3.53 in [89.66 mm]
Weight	1.102 lbs [499.86 g]
<b>Interface</b>	
Waveguide Size	WR-159
Flange Type	CPR-159F
RF Connector Type	N Female
Coupler Body Material and Plating	Aluminum, Chromate

### Environmental Specifications

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

### Features:

- Three Port Crossguide Waveguide Coupler
- 30±1.5 dB Nominal Coupling Level
- Integrated N Female Connector for the coupled port
- 4.64 GHz to 7.05 GHz Frequency Range
- Low VSWR < 1.25:1

### Applications:

- Test Benches
- Radar
- Satellite
- Microwave Radio
- Attenuation Measurements
- Power Measurements
- Source Leveling

Fairview Microwave  
 301 Leora Ln., Suite 100  
 Lewisville, TX 75056  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)


30 dB WR-159 Waveguide Crossguide Coupler with CPR-159F Flange and N Female Coupled Port from 4.64 GHz to 7.05 GHz in Aluminum from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [30 dB WR-159 Waveguide Crossguide Coupler with CPR-159F Flange and N Female Coupled Port from 4.64 GHz to 7.05 GHz in Aluminum FMWCP1082-30](#)

URL: <https://www.fairviewmicrowave.com/30-db-wr-159-waveguide-crossguide-coupler-fmwcp1082-30-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





T-Rev.D